



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [951463](#) > [951463BGLF](#)

[Add to myIDT \[?\]](#)

You may also like...

951463BGLF

Category:

Generic Part: [951463](#)

Market Group: PC CLOCK

Description: ICS

The ICS951463 is a main clock synthesizer chip that provides all clocks required for ATI RS600-based systems. An SMBus interface allows full control of the device. Output Features: â€¢ 3 - 0.7V current-mode differential CPU pairs
â€¢ 6 - 0.7V current-mode differential SRC pairs
â€¢ 2 - 0.7V current-mode differential ATIG pairs
â€¢ 2 - 48MHz USB clock
â€¢ 3 - 14.318MHz Reference clock

**Time is
money**

Parameters

Package	TSSOP 56 (PAG56)
Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	102
Factory Order Increment	34

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Description	TSSOP 6.10 MM
Class	PLASTIC
Moisture Sensitivity Level (MSL)	1
Category	Green
Moisture Exposure Floor Life	Unlimited @ <30°C/85% RH
Peak Reflow Temperature	260°C
Rebake Conditions	N/A
Length	14.0
Mark	G
Width	6.1
Pitch	0.5
Thickness	1.0
Status	Active

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. **All Rights Reserved.**