



PART NUMBER	TAB SIZE	WIRE RANGE AWG	MAX. INSUL. DIA.	DIMENSIONS in.		
				A $\pm .03$	B $\pm .01$	C $\pm .01$
DNF18-110	.110 X .032 (2.8 X 0.8)	.22-18 (0.5-1.0)	.100 (2.54)	.69 (17.5)	.15 (3.8)	.08 (2.0)
DNF18-111	.110 X .020 (2.8 X 0.5)	.22-18 (0.5-1.0)	.100 (2.54)	.69 (17.5)	.15 (3.8)	.07 (1.8)

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 300V. MAX. VOLTAGE RATING
 - B. #22-18 AWG STRANDED COPPER WIRE ONLY
 - C. 194° F (90° C) MAX. TEMP. RATING
2. MATERIAL:
 - A. STAMPING - .010" (0.25) THK BRASS, TIN PLATED
 - B. SLEEVE - BRASS, TIN PLATED
 - C. HOUSING - NYLON, RED
3. PACKAGE QTY:
 - STD. PKG. -C= 100
 - BULK PKG. -M= 1000
4. INITIAL INSERTION FORCE - 12 LB. (53 N)
INITIAL WITHDRAWAL FORCE - 12 LB. (53 N)
6 LB. (27 N)
5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
6. INSTALLATION TOOLS:
 - A. UL LISTED & CSA CERTIFIED: CT-520, CT
 - B. PANDUIT RECOMMENDED: CT-100
7. WIRE STRIP LENGTH: 9/32 $^{+1/32}_{-0}$ (7.1 $^{+.8}_{-0}$)



U_L

LISTED
20H3
E78522

A blue circular logo with the letters 'SA' inside, representing the Society of American Architects.

CERTIFIED
LR31212

A41308_05

05	7/03	KLFU		UPDATED DRAWING				 PANDUIT CORP.	TINLEY PARK, ILLINOIS					
04	5/98	TM	JW	ADDED CT-1525 TO TOOL NOTES	06872	LA	DH							
03	6/95	MS	RS	UPDATED NOTES AND DIMENSIONS	03370	LA	KS							
02	11/94	TH	RS	UPDATED NOTES AND DIMENSIONS	02689	LA	TK							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	DAW	CHK'D	SCALE	NONE	DRAWING NO.	A41308

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DNF18-111-C](#) [DNF18-111-M](#)