



LOC		DIST		REV		REVISIONS		DATE	APPD
G	14	P	F	ZONE	LTR	DESCRIPTION			
						REVISED & REDRAWN PER 0720-0040-93		4-8-93	1 st DAP
						REACTIVATED 324209 PER 0720-6018-92			

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed
12-10 AWG SOLID OR STRANDED		12-10 AWG STRANDED
LR7189 Certified		MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED		NOT APPLICABLE

1 STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² (5,180-13,100) CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
WITHOUT NOTICE. ANY REVISIONS TO THIS
DRAWING SHALL BE CONTAINED IN THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC # - 3 PLC DEC # - ANGLES	DR 4-8-93 TA BRINKMAN CHK 4-8-93 DA PATTERSON APPD 4-8-93 DE MILLER APPD 4-8-93 JL MECKLEY PRODUCT SPEC FINISH TIN PLATE 0.00254 [0.000100] MIN THK PER MIL-T-10727
--	--

DR 4-8-93 TA BRINKMAN CHK 4-8-93 DA PATTERSON APPD 4-8-93 DE MILLER APPD 4-8-93 JL MECKLEY PRODUCT SPEC FINISH TIN PLATE 0.00254 [0.000100] MIN THK PER MIL-T-10727	APPLICATION SPEC WEIGHT -
--	------------------------------

NAME	AMP	AMP Incorporated Harrisburg, PA 17105-3608
QUANTITY	2500	ON TAPE
PACKAGING TYPE	LOOSE PIECE	324209
PART NO		
SIZE	00779	CAGE CODE
DRAWING NO	00779	324209
SCALE	8:1	SHEET

TERMINAL, HOOK
TONGUE, SOLISTRAND™