





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NO.* | MAT'L<br>SUFFIX | MATERIAL                | MOUNTING<br>RIVET | 'A'              | 'B'              | 'C'            | 'D'            | 'E'            | 'F'            | USE WITH THESE<br>CABLE TIE<br>CROSS SECTIONS      | WEIGHT (g)<br>lbs/100 pcs. |
|----------------------|-----------------|-------------------------|-------------------|------------------|------------------|----------------|----------------|----------------|----------------|----------------------------------------------------|----------------------------|
| TM2R6                | NONE            | NYLON 6/6               | #6 (M3)           | 0.630<br>[16.0]  | 0.425<br>[10.8]  | 0.275<br>[7.0] | 0.215<br>[5.5] | 0.060<br>[1.5] | 0.155<br>[3.9] | MINIATURE<br>INTERMEDIATE<br>STANDARD              | 0.127<br>(57.8)            |
|                      | -0              | WEATHER RESISTANT NYLON |                   |                  |                  |                |                |                |                |                                                    |                            |
|                      | -30             | HEAT STABILIZED NYLON   |                   |                  |                  |                |                |                |                |                                                    |                            |
| TM3R6                | NONE            | NYLON 6/6               | #6 (M3)           | 0.860<br>[21.84] | 0.610<br>[15.94] | 0.375<br>[9.5] | 0.320<br>[8.1] | 0.088<br>[2.2] | 0.210<br>[5.3] | MINIATURE<br>INTERMEDIATE<br>STANDARD<br>LT. HEAVY | 0.371<br>(168.3)           |
|                      | -0              | WEATHER RESISTANT NYLON |                   |                  |                  |                |                |                |                |                                                    |                            |
|                      |                 |                         |                   |                  |                  |                |                |                |                |                                                    |                            |



- \* NOTES:  
1. SEE CURRENT PRICE SHEET FOR PART  
NUMBER SUFFIX DESIGNATION FOR  
PACKAGE SIZE.

SECTION A-A

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYER: G00239BU\_PB\_TMR\_09

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

TIE MOUNT  
TM2R6 & TM3R6

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X)  $\pm 0.05$  (1.3) (.XXX)  $\pm 0.010$  (0.25)  
(.XX)  $\pm 0.02$  (0.5) ANGLES  $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

|     |         |     |     |                                 |          |   |      |     |  |                  |                     |               |          |
|-----|---------|-----|-----|---------------------------------|----------|---|------|-----|--|------------------|---------------------|---------------|----------|
| 9   | 4/5/04  | JAD |     | REMOVE -30 OPTION FOR TM3R6     | GB0239BU | 9 |      |     |  | DRAWN BY<br>DWP  | MAT'L:<br>SEE TABLE | SCALE<br>NONE |          |
| 8   | 3/16/04 | JAD |     | CHANGE DIM 'A' AND 'B' ON TM3R6 | GB0239BU | 8 |      |     |  | DATE<br>04/15/96 |                     | DRAWING NO.   | DWG<br>A |
| REV | DATE    | BY  | CHK | DESCRIPTION                     | ECN      | R | CUST | SUP |  | GR'D             |                     | GB0239BU      | SIZE     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[TM2R6-M0](#) [TM2R6-M30](#)