







REV.	DATE	DESCRIPTION
NC	10/25/02	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S

- CRIMP NOTES:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
 2. CRIMPED CONTACT PIN
SQ. CRIMP SIZE .7mm
 3. MAX. PANEL THICKNESS = 7mm

9	HEX NUT	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	Amphenol - Connex CONNECTOR CORPORATION TNC BULKHEAD CRIMP JACK (FOR RG-316/U, 174/U, 188A/U CABLE)					
8	LOCK WASHER	BRASS	NICKEL									
7	FERRULE	COPPER	NICKEL									
6	CONTACT PIN	BRASS	GOLD		DRAWN	G.R.S.						10/25/02
5	BARREL	BRASS	NICKEL		CHECKED							
4	LOCK RING	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"	ISSUED		TITLE					
3	CONTACT PIN	PHOS. BRONZE	GOLD									
2	INSULATOR	TEFLON	NATURAL									
1	BODY	BRASS	NICKEL									
	DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING			SCALE	NA	PART NO.	122487	SHEET	1 OF 1