






Terminal No.1 Terminal No.5






Metal tab (Front)
(Improvement of
wrench strength)

DIP-TYPE (Back)



DETAIL "A"

No.	Part Name	Material	Finish	Remarks
1	Scoket Housing	Thermoplastic	(Black)	
2	Scoket Contact Ter	Copper Alloy	Au over Ni	
3	Scoket Shield	Stainless Steel	Sn over Ni	
4	Scoket Plate	Stainless Steel		



RECOMMENDED PCB Pattern

(Tolerance : ±0.05)

-NOTE-

1. This product is enable to mount both
USB-IF Recommended PCB pattern and
NEW USB-IF Recommended PCB Pattern
2. Coplanarity : The dimension between flat tool and
when connector put on the flat tool like PCB
bottom of soldering terminals
Signal terminal / Metal (front) : Max 0.08 mm
3. PRODUCT NUMBERING
10103594 - 0001 LF

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.38	.XX ± 0.25	projection	title	www.fciconnect.com	
A	T10-0002	J.H	1/7/10		.XXX ± 0.15	0° ± 2°				
				angles						
				dr	JASON HSU	1/7/10				
				enr	JASON HSU	1/7/10				
				chr	GARY HSIEH	1/7/10				
				appd	JOSEPH HSIA	1/7/10				
sheet	revision	A								
index	sheet	1								