

Cable and Bolt Cutters

Klein exceeds the highest standards to create superior cable and bolt cutters, offering greater cutting power, clean and precise cuts, as well as long life. Klein cable and bolt cutters are a cut above the rest.



For Professionals...
Since 1857™



Plastic-dipped handles
for comfort and ease
of identification

FORGED STEEL

from Klein's US-made,
proprietary blend

Cable Cutters

Hot-riveted joint
ensures smooth action
and no handle wobble

Through-hardened
(not case-hardened) for
longer-lasting cutting surfaces

Beveled jaw tips
provide proper mating and
shearing action, which
protects leading jaw edges



High-Leverage Cable Cutters

Additional Features:

- High-leverage design for exceptional cutting capability
- Precision, one-hand shearing action
- Cable-gripping shear-type jaws
- Perfect for working in confined spaces
- Can be carried in most tool pouches



63050

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Handle Color	Handle Finish	Weight
63050	9-1/2" (241.3 mm)	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	Red	Plastic-dipped	14.4 oz. (408 g)
Journeyman Series – Dual-material handles					
J63050	9-9/16" (242.9 mm)	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	Red/Black	Journeyman	15.7 oz. (445 g)

Cable Cutters - Coaxial

Additional Features:

- Cable-gripping jaws quickly score jacket and insulation, and easily cut through copper inner conductor
- Blades cleanly cut aluminum and copper coaxial cable without compression and frayed ends
- Forged body with heat-treated and precision-ground steel blade withstands frequent cutting
- Hot-riveted design requires no adjustment while maintaining a smooth, precise operation
- Compact, lightweight design fits perfectly in any professional's tool pouch
- When cutting drop wire with an inner steel conductor, we recommend our 2000 Series cutting pliers



63028



63030

⚠ WARNING: Do NOT cut steel or ACSR.

Cat. No.	Handle Color	Overall Length	Soft Cable-Cutting Maximum Capacity	Weight
63028	Yellow	8-1/4" (209.6 mm)	3/4" (19.1 mm)	12.8 oz. (363 g)
63030	Blue	8-1/4" (209.6 mm)	1" (25.4 mm) Diameter	13.3 oz. (377 g)



Cable Cutters

Compact Cable Cutter

Additional Features:

- Precise, one-hand shearing action cuts 24 AWG copper, aluminum multi-strand cable and wire, and 100-pair telephone cable
- Special shear angle cuts cleanly without compression to cable geometry for telecom cable work
- Heat-treated, high-carbon steel shearing edges for long life
- Forged body with 3/8" (10 mm) case-hardened rivet



63055

⚠ WARNING: Do NOT cut steel or ACSR.

Cat. No.	Handle Color	Overall Length	Maximum Cable Cutting Capacity	Weight
63055	Red	8" (203.2 mm)	24 AWG Copper, Aluminum Multi-Strand Cable and Wire, and 100-Pair Telephone Cable	10.4 oz. (295 g)

All-Purpose Shears and BX Cutter

Additional Features:

- High-leverage, shear-type design for one-hand operation
- Lightweight and compact
- Stripping notch for added convenience
- Cuts BX cable, sheet metal, steel strapping, and bundling wire
- Handle cavity is designed to restore BX cable to original shape after cutting



1104

⚠ WARNING: Do NOT cut steel or ACSR.

Cat. No.	Handle Color	Overall Length	Length of Cut	Weight
1104	Red	7-5/8" (193.7 mm)	7/8" (22.2 mm)	9.6 oz. (272 g)

Heavy-Duty Cable Shears

- Heavy-duty, tempered steel blades
- Cuts ACSR, steel, and most hardened wire
- Blades grip cable and cut easily at center of jaws
- Lock keeps handles closed for easy storage
- Comfortable, plastic-coated handles for steady grip
- Hardened steel, precision cutting blades for long service life
- Unique triangular jaws cleanly cut cable without compression or frayed ends



63016

Cat. No.	Handle Color	Overall Length	Maximum Cable Cutting Capacity	Weight
63016	Blue	7-1/2" (190.5 mm)	Up to 1/4" (6.4 mm) Copper and Mild Steel Strands, up to 3/16" (4.8 mm) Aircraft Cable, Wire Rope, Aluminum and Copper Rods, up to 5/32" (4.0 mm) for Steel and Iron Rods	10.4 oz. (295 g)

Multi-Cable Cutter KLEIN-KURVE™

- Hardened steel precision-ground cutting blades for long life
- Copper curved cutter cleanly cuts round copper cable without compression or frayed ends
- Anvil cutter for solid and stranded copper wire up to 12 AWG and stainless steel up to 0.032" (0.81 mm) diameter
- Mild steel cutter for conductors up to 0.080" (2 mm) diameter
- Curved cutter for solid and stranded copper wire up to 8 AWG, multi-conductor cable up to 1/2" (13 mm) diameter and coaxial cable RG-6 Quad, RG-59, and RG-62
- Double-dipped grips for comfort
- Coil spring provides fast self-opening action
- Holes for looping and bending wire
- New lock design for convenient storage also prevents accidental locking and loosening over time



63020



Cat. No.	Handle Color	Overall Length	Screw Shearing	Weight
63020	Red	7" (177.8 mm)	6-32 & 8-32	7.0 oz. (198 g)



Cable Cutters

Utility Cable and Rope Cutters

- Forged steel with black-oxide finish for long life
- Shear-type hook jaws grab and hold cable while shear-cutting action makes clean cuts
- Beveled tips for positive mating
- Hinge bolt with pin-set nut for proper blade tension
- Cat. No. 63035SC cuts wire up to 9/32" (7 mm) and Stoffel® container seals
- Cat. No. 63035 is not designed to cut steel or ACSR



Cat. No.	Handle Color	Overall Length	Maximum Cable Cutting Capacity	Weight
63035	Red	16-1/4" (412.8 mm)	MCM Cable 350 Copper, 350 Aluminum	1.7 lbs. (0.77 kg)
63035SC	Red	18" (457.2 mm)	9/32" (7.1 mm) Wire Rope and Cables	2.0 lbs. (0.91 kg)

Standard and Communication Cable Cutters

- Lightweight, yet efficient shear-type cable cutters
- Replaceable hook-jaw blades grab and hold cable while shear-cutting action makes clean cuts
- Exceptionally strong fiberglass handles with heavy vinyl grips for comfort and slip resistance
- Heavy-duty pins in head serve as blade-stops
- Jaws are forged tool steel with black-oxide finish for long life
- Beveled tips assure positive mating, and hinge on a rugged bolt with a pin-set nut to maintain proper blade tension
- Makes a clean, even cut for ease in fitting lugs and terminals
- Cat. No. 63041TH includes rubber sleeves
- Cat. No. 63047 cuts lead or rubber-covered communications cable



WARNING: Do NOT cut steel or ACSR.

Cat. No.	Soft Cable-Cutting Maximum Capacity	MCM Cable-Cutting Maximum Capacity	Overall Length	Weight
63041	1-3/8" (34.9 mm) Diameter	500 Copper, 750 Aluminum	25-1/2" (647.7 mm)	5.3 lbs. (2.40 kg)
63041TH	1-3/8" (34.9 mm) Diameter	500 Copper, 750 Aluminum	25-1/2" (647.7 mm)	5.3 lbs. (2.40 kg)
63045	1-3/4" (44.5 mm) Diameter	1000 Copper, 1200 Aluminum	32" (812.8 mm)	8.0 lbs. (3.63 kg)
63047	Up to 2-1/4" (57.2 mm) Diameter	900-Pair Soft Copper and Aluminum	37" (939.8 mm)	8.6 lbs. (3.90 kg)

Replacement Cable Cutter Heads (complete)

Cat. No.	For Use With	Weight
63081	63041	2.1 lbs. (0.95 kg)
63090	63045	3.3 lbs. (1.50 kg)
63110	63047	3.5 lbs. (1.59 kg)



Cable Cutters

Ratcheting Cable Cutters

- High-leverage ratchet mechanism for single-handed cutting of copper and aluminum cables, leaving no burrs or sharp edges
- Requires fewer strokes per cut
- Open jaw design works in confined spaces (Cat.No. 63711)
- Quick-release lever opens blades easily in every cutting position (Allows removal of the cable before completion of cut)
- Holds cables tight and allows rapid, straight cuts with minimum effort
- Hardened steel cutting blades for lasting strength and sharpness
- Plastic covered handles with hand guards for comfort and firm grip
- Locking lever keeps handles closed for easy transport; fits in a toolbox or bag
- One-year warranty (Cat. No. 63060 & 63750)

WARNING: Do NOT cut steel or ACSR.

Replacement parts available

(blades, handles, springs, pawl sets and release plates).

Go to www.kleintools.com or call 800-553-4676


for a full listing of replacement parts.



63060



63711



63750

Cat. No.	Handle Color	Overall Length	MCM Maximum Cable Capacity (Copper)	MCM Maximum Cable Capacity (Aluminum)	MCM Maximum Cable Capacity (Communication Cable)	Weight
63060	Red	10-1/4" (260.4 mm)	400 MCM (185 mm ²)	600 MCM (300 mm ²)	1-1/8" (28.6 mm)	1.3 lbs. (0.59 kg)
63711	Red	11-1/2" (292.1 mm)	600 MCM (300 mm ²)	750 MCM (400 mm ²)	1-1/8" (28.6 mm)	2.0 lbs. (0.91 kg)
63750	Red	12-1/8" (308.0 mm)	1000 MCM (500 mm ²), Frequent Use: 750 MCM (400 mm ²)	1000 MCM (500 mm ²), Frequent Use: 750 MCM (400 mm ²)	2-1/16" (52.4 mm)	1.8 lbs. (0.82 kg)

ACSR Ratcheting Cable Cutter

- High-leverage ratcheting mechanism for easier cutting
- Quick-release lever opens blades easily in every cutting position. (Allows removal of the cable before completion of cut)
- Hardened steel cutting blades for long lasting strength and sharpness
- Tools can be locked when not in use
- Cat. No. 63800ACSR features cutting inserts that are easily replaced by simply removing 3 screws per blade

Replacement parts available

(blades, handles, springs, pawl sets and release plates).

Go to www.kleintools.com or call 800-553-4676

for a full listing of replacement parts.



63607



63800ACSR

Cat. No.	Handle Color	Overall Length	MCM Maximum Cable Capacity (Copper)	MCM Maximum Cable Capacity (Aluminum)	MCM Maximum Cable Capacity (ACSR)	MCM Maximum Cable Capacity (Guy Strand)	Weight
63607	Yellow	10-1/4" (260.4 mm)	400 MCM (185 mm ²)	600 MCM (300 mm ²)	336 MCM (170 mm ²)	—	1.5 lbs. (0.68 kg)
63800ACSR	Red	13-3/4" (349.3 mm)	1" (25.4 mm)	1-1/4" (31.8 mm)	477 MCM (273 mm ²)	1/2" (12.7 mm)	3.2 lbs. (1.45 kg)



Cable Cutters

Ratcheting ACSR Cable Cutter - Heavy-Duty



63700

- Ratchet-action design provides maximum leverage with minimum effort for heavy-duty use
- Blade-advance knob for fast rotation of the blade to engage the cable or other material being cut, plus a quick-release mechanism allows for removal of the cable or rod before completion of the cut, if desired
- Not designed for cutting EHS guy strand or reinforcement rod
- Cuts steel and ACSR
- Forged, heat-treated, shear-type blades, plus 17" (432 mm) long fiberglass handles with heavy duty grips for comfort and slip resistance

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	Steel Cable-Cutting Maximum Capacity	Weight
63700	28" (711.2 mm)	2-1/4" (57.2 mm) Diameter, 750 MCM (1-3/8" [34.9 mm]) Diameter, Copper or Aluminum	1-1/4" (31.8 mm) Diameter ACSR, ACAR, 7/16" (11.1 mm) Diameter Common Guy Strand, 5/8" (15.9 mm) Diameter Steel Wire Rope, 1/2" (12.7 mm) Diameter Steel Rod (C.R.S. SOFT)	14.0 lbs. (6.35 kg)

Bolt Cutters

Heavy-Duty Ratcheting Bolt Cutter

- Cuts 1/2" utility-grade guy strand, 3/8" EHS
- Spring-loaded cable retention hook snaps onto the cable in one hands-free motion and keeps strands between cutting blades
- Long handles provide leverage when cutting
- Lockplate reinforcement prevents jaw bolts from loosening or turning, keeps jaws in correct alignment



63RBCHD

**EASY
AS**



OPEN

movable handle to full extension to open cutting jaws



SNAP

cable between cutting jaws



CUT

cable using ratcheting handle

Cat. No.	Cutting Capacity	Up to HRC	Overall Length	Weight
63RBCHD NEW!	1/4" - 1/2" (6.4 - 12.7 mm) Guy Strand up to 3/8" (9.5 mm) EHS	Rockwell C31, Rockwell C42	31" (787.4 mm)	10 lbs. (4.54 kg)



Bolt Cutters

Bolt Cutters - Steel and Fiberglass Handle

- All-purpose, center-cut jaws
- Forged, alloy tool steel jaws are precision ground for sure, efficient cutting and long life
- Lock plate reinforcement prevents jaw bolts from loosening or turning, keeping jaws in correct alignment
- NOT for cutting cable



63314

Cat. No.	Handle Type	Overall Length	Soft & Medium Cutting Max. Capacities	Hard Material Cutting Max. Capacities	Weight
Steel Handles					
63314	Steel	14" (355.6 mm)	5/16" (7.9 mm)	3/16" (4.8 mm)	3.2 lbs. (1.45 kg)
63318	Steel	18" (457.2 mm)	3/8" (9.5 mm)	1/4" (6.4 mm)	3.6 lbs. (1.63 kg)
63324	Steel	24" (609.6 mm)	7/16" (11.1 mm)	5/16" (7.9 mm)	6.3 lbs. (2.86 kg)
63330	Steel	30" (762.0 mm)	1/2" (12.7 mm)	3/8" (9.5 mm)	10.2 lbs. (4.63 kg)
63336	Steel	36" (914.4 mm)	9/16" (14.3 mm)	7/16" (11.1 mm)	14.3 lbs. (6.49 kg)
63342	Steel	42" (1066.8 mm)	11/16" (17.5 mm)	1/2" (12.7 mm)	19.2 lbs. (8.71 kg)
Fiberglass Handles					
63118	Fiberglass	18-1/4" (463.6 mm)	3/8" (9.5 mm)	1/4" (6.4 mm)	3.7 lbs. (1.68 kg)
63124	Fiberglass	24-1/2" (622.3 mm)	7/16" (11.1 mm)	5/16" (7.9 mm)	6.1 lbs. (2.77 kg)
63130	Fiberglass	30-1/2" (774.7 mm)	1/2" (12.7 mm)	3/8" (9.5 mm)	9.5 lbs. (4.31 kg)
63136	Fiberglass	36-1/2" (927.1 mm)	9/16" (14.3 mm)	7/16" (11.1 mm)	13.0 lbs. (5.90 kg)

* Up to Brinell 300, Rockwell C31. ** Up to Brinell 400, Rockwell C42.

Replacement Blades

Cat. No.	For Use With	Weight
63224	63124	2.00 lbs. (0.9 kg)
63814	63314	0.81 lbs. (0.37 kg)
63818	63318	1.22 lbs. (0.55 kg)
63824	63324	1.94 lbs. (0.88 kg)
63831	63330	3.06 lbs. (1.39 kg)
63836	63336	4.50 lbs. (2.04 kg)
63842	63342	6.03 lbs. (2.74 kg)

Replacement Fiberglass Handle Sets

63131	63130	5.00 lbs. (2.27 kg)
63137	63136	7 lbs. (3.2 kg)

Cable Benders

- Durable forged and one-piece steel construction for exceptional strength
- Head is angled 22° for ease in bending cable in tight, hard-to-access places
- Corrosion-resistant, black-oxide finish with heavy-duty double-dipped plastic handle
- It is recommended that two benders be used for easier bends



50400

Cat. No.	Overall Length	Tool Opening	Maximum Cable Capacity	Weight
50400	12" (304.8 mm)	7/8" (22.2 mm)	350 MCM	14.4 oz. (408 g)
50402	14-1/2" (368.3 mm)	1-1/64" (25.8 mm)	500 MCM	1.6 lbs. (0.73 kg)

