


Model 2BA-AL & 2BC-AL Double Banana Plug To Alligator Clip Breakouts Cable Assembly



MATERIALS:

Double Banana Plug:

Plug Bodies: Brass, Nickel Plated

Springs: Beryllium Copper, Nickel Plated

Insulation: Polypropylene Molded to the Plug Bodies and Cable. Color Matches Color of Cable.

Marking: POMONA ELECTRONICS CO., INC. POMONA CALIFORNIA

Cable: 2BA: 2 COND. Tw. 18 AWG. 65 x 36 t.c., .250 (6,4) O.D., Marking: POMONA 2BA-AL-XX

Color: Gray. 2BC: RG-58C/U, .195 (5,0) O.D., Marking: POMONA 2BC-AL-XX, Color: Black.

Molded Breakout: PVC Insulated Molded to Breakout Leads and Cable. Color Matches Color of Cable.

Breakout Leads: 20 AWG 41 x 36 t.c., PVC Insulated, .087 (2,21) O.D., Color Matches Color of Insulator.

Insulated Alligator Clips: Body: Steel, Nickel Plated, Insulator: Vinyl. Color: One Black and One Red.

RATINGS:

Operating Temperature: +50°C Max.

Operating Voltage: 2BA: 150 VRMS/DC

Current: 5 Amperes

ORDERING INFORMATION: Model 2B*-AL-XX

XX = Cable Lengths, Standard Lengths: 18" (457,2cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

* = Cable Type, 2BA: 2 Cond. Twisted Pair, 2BC: RG 58C/U.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA