



2002-11-18

PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr

48-377-46	Koppl plint vinkl 2-pol	COB 5/2
48-377-53	Koppl plint vinkl 3-pol	COB 5/3
48-377-61	Koppl plint vinkl 2-pol	COB 10/2
48-377-79	Koppl plint vinkl 1-pol	COB 10/1A




**MORSETTIERE PER C.S.
TERMINAL BLOCKS FOR P.C.B.
BARRETTES DE CONNEXION POUR C.I.
ANSCHLUßKLEMMEN FÜR LEITERPLATTE**

TIPO
TYPE
TYPE
TYP

COB

PASSO
PITCH
PAS
RASTERMAß

5 10 mm



MODULI COMPONENTI
A CARRELLO
2/3 POLI

ISING CLAMP
INTERLOCKING MODULES
2/3 POLES

BORNE ETRIEZ MOBILE
ELEMENTS MODULAIRES
2/3 POLES

BEWEGLICHER
KLEMMKÖRPER
2/3 POLIG ANREIHBAR



Corpo isolante Grigio	Insulating body Grey	Corps isolant Gris	Isolierkörper Grau	PA68 UL94VO
Vite	Screw	Vis	Schraube	M2,5-CB15+Zn
Morsetto	Clamp	Borne	Klemmkörper	C60+Zn
Contatto	Pin	Contacte	Kontakt	CuZn37+Ni+Sn
Coppia di torsione	Testing torque	Couple de serrage	Zul. Drehmoment	0,4 Nm
Sezione	Section	Section	Querschnitt	1,5 mm ²
Foro di montaggio	P.C.B. mounting hole	Perçage C. I.	Leiterplattenbohrung	Ø 1,3 mm
Corrente nominale	Nominal current	Courant nominal	Strombelastbarkeit	17,5 A
Tensione	Voltage	Tension	Betriebsspannung	130/750 V
Temperatura	Temperature	Température	Temperatur	85°C
Grado di protezione	Protection index	Degré de protection	Schutzklasse	IP00
Resistenza di isolamento	Insulation resistance	Résistance d'isolement	Isolationswiderstand	≥ 5 MΩ
Rigidità dielettrica	Dielectric strength	Rigidité diélectrique	Durchschlagsfestigkeit	≥ 1250 Vac/60"

Ref. EN 60998-1

SCHEMA
PER ORDINAZIONE

ORDER
SCHEME

TABEAU
DE COMMANDE

BESTELLSCHHEMA

P	p	
Passo	N° di Poli	Numerazione
Pitch	Nr. of Poles	Printing
Pas	Nb. Pôles	Marquage
Rastermaß	Polzahl	Bedruckung
5 10	MIN 2÷ MAX ...	
COB	 /	Nu