


3.5mm 4 Conductor Panel Jack

161-5435-EX

KOBICONN

3.5mm 4 Conductor Panel Jack



Dimensions: mm (in.)
(except where noted)

SPECIFICATIONS	
Dielectric strength	500VAC for one minute
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC
Mating plug:	171-7435
RoHS Compliant by Exemption	

Date Last Revised: 06-06-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300961

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-5435-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-5435-EX](#)