




OBSOLETE

-	4.34±0.08 [.171±.003]	#8	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00457[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277148-8
14.8 ±3 GRAMS	6.73±0.13 [.265±.005]	1/4		277148-7
15.2 ±3 GRAMS	5.00±0.08 [.197±.003]	#10		277148-6
17.0 ±3 GRAMS	4.34±0.08 [.171±.003]	#8		277148-5
15.3 ±3 GRAMS	9.91±0.13 [.390±.005]	3/8		277148-4
16.2 ±3 GRAMS	8.33±0.13 [.328±.005]	5/16		277148-3
-	6.73±0.13 [.265±.005]	1/4		277148-2
16.8 ±3 GRAMS	5.00±0.08 [.197±.003]	#10		277148-1
WEIGHT	'A'	'B'	MATERIAL & FINISH	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 6/23/89 CHK MS FEHER 10/16/90 APVD AJ KAUFMAN 10/23/90 PRODUCT SPEC 108-11011 APPLICATION SPEC 114-2134 WEIGHT SEE TABLE CUSTOMER DRAWING	TE Connectivity WIRE TERMINAL, RING TONGUE, SEALED COPALUM 14.6mm2 [6] ALUMINUM 8.8mm2 [8] COPPER SIZE A2 CAGE CODE 00779 DRAWING NO C=277148 RESTRICTED TO -
DIMENSIONS: MM [INCHES]			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH SEE TABLE	SCALE 4:1 SHEET 1 of 1 REV P