

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202350005

Status:


Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Power Connector, Straight Male Receptacle Housing Only, Cable Diameter 7.00-12.00mm



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                      |
|-------------------------------|--------------------------------------|
| General                       |                                      |
| Product Family                | Field Attachable / Accessories       |
| Series                        | 120235                               |
| Application                   | Power                                |
| IP Rating                     | IP67                                 |
| Material - Contact            | Brass                                |
| Overview                      | Brad M23 Signal and Power Connectors |
| Product Name                  | Brad M23                             |
| Type                          | Field Attachable Connector           |
| UPC                           | 883906301859                         |
| Physical                      |                                      |
| Cable Diameter                | N/A                                  |
| Coupling Type                 | N/A                                  |
| Diagnostics / LEDs            | No                                   |
| Diagnostics Port              | No                                   |
| Gender                        | Male                                 |
| Keyway                        | None                                 |
| Material - Connector Body     | Nylon                                |
| Material - Coupling Nut       | N/A                                  |
| Material - Plating Mating     | Gold                                 |
| Net Weight                    | 79.400/g                             |
| Orientation                   | Straight                             |
| Poles                         | N/A                                  |
| Temperature Range - Operating | -40°C to +125°C                      |
| Wire Size AWG                 | N/A                                  |
| Electrical                    |                                      |
| Current - Maximum per Contact | N/A                                  |
| Voltage - Maximum             | N/A                                  |
| Material Info                 |                                      |
| Engineering Number            | KAP0S06-005                          |
| Reference - Drawing Numbers   |                                      |
| Sales Drawing                 | SD-120235-026                        |

|                                               |               |
|-----------------------------------------------|---------------|
| EU ELV                                        |               |
| Not Relevant                                  |               |
| EU RoHS                                       | China RoHS    |
| Compliant with Exemption 6(c)                 |               |
| REACH SVHC                                    |               |
| Contained Per - D(2020)4578-DC (25 June 2020) |               |
| Lead                                          |               |
| Halogen-Free                                  |               |
| Status                                        |               |
| Not Low-Halogen                               |               |
| For more information, please visit Contact US |               |
| China ROHS                                    | 50 Image      |
| ELV                                           | Not Relevant  |
| RoHS Phthalates                               | Not Contained |

Search Parts in this Series

120235 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION