




TOLERANCES				
APPLY TO DESIGN UNITS. DIMENSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 5				
	INCH	MILLIMETER	INCH TO MILLIMETER	MILLIMETER TO INCH
NO PLACES	± .010	± .25	1:1	0.001
ONE PLACE	± .005	± .13	1:1	0.001
TWO PLACES	± .002	± .05	1:1	0.001
THREE PLACES	± .001	± .02	1:1	0.001
FOUR PLACES	± .0005	± .01	1:1	0.001

DESIGN UNITS

RAW MATERIAL—COMMERCIAL STEEL

MILCO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

WEIGHT

- 1 - MOUNTING SCREW HOLES, 10-32 UNF-2B THREADS X .219 REF. DEEP (8)
- 2 - LEAD WIRES 105°C MAX
- 3 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A RAPID STROKE TO THE SWITCH ROLLER
- 4 - EXPLOSION PROOF-UNDERWRITER'S LAB INC LISTING FOR HAZARDOUS LOCATIONS, NEMA 7, CLASS I, GROUP C & D, NEMA 9, CLASS II, GROUPS E, F, & G
- 5 - N.O. LEADS - BLUE
N.C. LEADS - RED
GROUND LEAD - GREEN
- 6 - SEAL RATING: NEMA 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[15PA261-CX](#)