




ARRANGEMENT OF CONTACTS							
PARTS	B2002-3P	B2002-4P	B2002-5P	B2002-5A	B2002-6P	B2002-7P	B2002-8P
ANGLE	180°	216°	180°	240°	240°	270°	270°
POSITION OF VIEWS							

SPECIFICATIONS	
Dielectric strength	1,000V AC/1 Minute
Contact resistance	20M Ω Max.
Insulation resistance	100M Ω Min. at 500V DC
Rating	100V AC 2A



4	GROUNDING	1	BSR-H (0.2t)	[C2680R]	SILVER PLATED	3-5U"
3	CONTACT TERMINAL	5	BSR-H (0.2t)	[C1519R-H]	SILVER PLATED	3-5U"
2	PLASTIC CORE	1	ABS	[777D]	BLACK	HB
1	METAL BODY	1	DIECAST		NICKEL	3-5U"
P/N	PART NAME	Q'TY	MATERIAL		PLATING	REMARKS

DRAWN	KIDD	APP'D		UNIT	mm	TOLERANCE .x ± 0.20 .xx ± 0.10 .xxx ± 0.05 .xxx ± 0.03 ANGULA $\pm 1^\circ$				TITLE	B2002-5P METAL DIN CIRCULAR SOCKET			SHEET 1
CHK'D				SCALE	1:1					PART NO.	B2002-5P	DWG NO.	METAL DIN	VERSION A