



Accessories EMF

Incandescent lamps

LED's

Mounting tools

Incandescent lamp T 1³/₄ Midget Groove




Order No.

	voltage	consumption	brightness	lifetime AC	DC
0913.4001	6.3 V	200 mA	.40 MSCP	50'000 h	25'000 h
0913.4002	14 V	80 mA	.20 MSCP	15'000 h	7'000 h
0913.4003	28 V	40 mA	.20 MSCP	10'000 h	5'000 h
0913.4004	48 V	25 mA	.20 MSCP	5'000 h	2'000 h
0913.4005	60 V	20 mA	.30 MSCP	1'000 h	1'000 h
0913.4006	24 V	50 mA	.18 MSCP	10'000 h	5'000 h

The use of incandescent lamps > 60 V is limited by different standards.

Series resistors for incandescent lamps and capacitors for the reduction of lamp voltage available on request. The permission for other ratings must be clarified according to the international testing laboratories. Incandescent lamps with lower power consumption on request.

LED T 1³/₄ Midget Groove



Order No.

	Operating voltage U _B [V]	Reverse voltage U _R [V]	Operating current I _F [mA]	Operating temperat. °C	Storage temperat. °C	Power dissipation P _{tot} [mW]	Peak wave length λ _{peak} [nm]	Reverse current I _R [μA]	Lumin. intensity I _V [mcd]
0925.0104 red	6	8	30	-25 °C up to +70 °C	-25 °C up to +85 °C	250	700	100	7
0925.0105 green	6	8	30			250	555	100	30
0925.0106 yellow	6	8	30			250	570	100	22
0925.0107 red	12	16	15			250	700	100	7
0925.0108 green	12	16	15			250	555	100	30
0925.0109 yellow	12	16	15			250	570	100	22
0925.0110 red	28	16	10			300	700	100	7
0925.0111 green	28	16	10			300	555	100	30
0925.0112 yellow	28	16	10			300	570	100	22

Lamp extractor



Order No.

0853.0621

Availability: ex warehouse or prompt delivery

Mounting key



Order No.

0853.0622