

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0780330128
Status: Obsolete
Description: 1.00mm (.039") Pitch Express Module (SIOM), Press-fit, 0.76µm (30µ") Gold (Au) Plating, 3.43mm (.135") Tail Length, with Plastic Pegs, 8 Ports, 98 Circuits, Tin/Lead

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	78033
Comments	PCI 8 ports
Component Type	Edgecard to PCB
Product Name	Express Module (SIOM)

Physical

(p)ower-(s)ignal Configuration	98s - 0p
Circuits (Loaded)	98
Circuits (maximum)	98
Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
PC Tail Length	3.43mm (.135")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.20mm (.126")
Packaging Type	Tray
Pitch - Mating Interface	1.00mm (.039")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	0.381µm (15µ")
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin


Electrical

Current - Maximum per Contact	1.1A
Voltage - Maximum	50V

Material Info

Reference - Drawing Numbers

Product Specification	PS-78033-001
Sales Drawing	SD-78033-001



EU RoHS RoHS Compliant by Exemption REACH SVHC Not Reviewed Low-Halogen Status Not Reviewed	China RoHS Pb
---	-----------------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
78033Series

Mates With
PCI Express Card