



Life's Good

Search all of LG

Monitors

E2340S

Class Size:

[Back to Monitors](#)

E2340S

[Where to Buy](#)

- OVERVIEW
- FEATURES
- GALLERY
- SPECIFICATIONS**
- SUPPORT

Share:   Compare {0} Recently Viewed {0}

Key Features



- Innovative LED (E40 Monitor)
- Overwhelming Excitement of Full HD
- Eco-Friendly Materials
- Slim Width of 17.5mm
- Photo Effect
- Mega Contrast Ratio
- [Expand all Specs](#)

GENERAL

Screen size (inches)	23
Panel Type (TN, IPS)	TN
Type	LED
HD Monitors	Yes
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness (cd/m2)	250
Contrast Ratio	1000:1
Response Time (ms)	5
Viewing Angle (°)	170 /160 (CR≥10)
Color Depth (Num of Colors)	16.7M
Pixel Pitch (mm)	0.265 x 0.265
Surface Treatment	Anti-Glare,3H

VIDEO

Max Input Resolution(Analog)	1920 x 1080
Max Input Resolution(Digital)	1920 x 1080
H-Scanning Frequency	30 ~ 83kHz
V-Scanning Frequency	56 ~ 75Hz

INPUT / OUTPUT

(Jack Position)	Rear
D-Sub	Yes

SPECIAL FEATURES

F Engine	Yes
sRGB	Yes
DDC/CI	Yes
Intelligent Auto	Yes
Plug & Play	DDC2B

SET COLOR

Front Color	BLACK ,High-Glossy
B/Cover Color	BLACK ,High-Glossy
Stand Color	BLACK ,High-Glossy
Base Color	BLACK ,High-Glossy
Color	Black

WEIGHT(KG)

Set with Stand (Kg)	3.16
Set without Stand (Kg)	3

STANDARD (CERTIFICATION) & VESA MOUNTING

UL(cUL)	Yes
TUV-GS	TUV-Type
SEMKO	Yes
FCC-B, CE	Yes

ACCESSORY

Power Cord	Yes
D-Sub	Yes

Recommended Products



[E2240S](#)
LG LED LCD Monitor. E40 Series



UK: English

[Contact Us](#) | [Sitemap](#) | [Glossary](#) | [Buyers' Guide](#) | [Jobs](#) | [Privacy](#) | [Legal](#) | [Low Bandwidth Site](#)
Copyright 2010 LG Electronics. All Rights Reserved.