


HYDRAULIC TOOLING

Wire Size	Dies for 59973-1, 69065		Dies for 69067 Flag• Terminals		59975-1, 69069 With/Self-Contained Dies	Dies for 58445-1 1752788-1	Dies for 69082 1752786-1	Dies for 69097		Dies for 69099 1752868-1
	Nest	Indenter	Nest	Indenter				Nest	Indenter	
8	48126	48355	48126• 48506•	48355• 48505•	59975-1 69069	----	----	46146	46145	69216
8 H.D.	48128-1	48127-1	48128-1	48127-1	----	----	----	----	----	---
6	48128	48127	48128• 48508•	48127• 48507•	59975-1 69069	----	----	46134	46133	69217
6 H.D.	48129-1	48127-1	48129-1	48127-1	---	---	---	---	---	---
4	48129	48127	48129• 48509•	48127• 48507•	59975-1 69069	---	---	46135	46133	69218
4 H.D.	48130-1	48127-1	48130-1	48127-1	---	---	---	---	---	---
2	48130	48127	48130• 48510•	48127• 48507•	59975-1 69069	---	---	46136	46133	45433
2 H.D.	48132-1	48131-1	48132-1	48131-1	---	---	---	---	---	---
1/0	48132	48131	48132• 48652•	48131• 48511•	---	---	---	46138	46137	45436
1/0 H.D.	48133-1	48131-1	48133-1	48131-1	---	---	---	---	---	---
2/0	48133	---	48133• 48805•	48131• 48511•	---	---	---	---	---	45439
3/0	48134	48131	48134• 48806•	48131• 48511•	---	---	---	---	---	45442
4/0	300430	---	300430• 48807•	48131• 48511•	---	---	---	---	---	45445
250-300 MCM	---	---	---	---	---	48816	69911	---	---	---
300-350 MCM	---	---	---	---	---	48817	69912	---	---	---
400 MCM	---	---	---	---	---	48818	69913	---	---	---
500-600 MCM	---	---	---	---	---	48819	69914	---	---	---

SOLISTRAND* Terminals and Splices
(Refer to pages 3, 4, and 5 for application tooling and accesasories.)




Pressure Type Wire Connector Chart (Use Type "W" Tooling)

WIRE SIZE RANGE	UL 424C LISTED	SP LR 7189 CERTIFIED
22-16 Solid or Stranded	22-16 Solid or Stranded	22-16 Solid or Stranded
16-14 Solid or Stranded	16-14 Solid or Stranded	16-14 Solid or Stranded
12-10 Solid or Stranded	12-10 Stranded	12-10 Solid or Stranded
8 Thru 600 MCM Solid or Stranded	8 Thru 600 MCM Stranded	8 Thru 4/0 Solid or Stranded


NOTE: 22-16 terminals and splices are stamped 22-18 in accordance with MIL-T-7928.

WIRE SIZE	HAND TOOLS †Long Handle ‡Heavy Head	PNEUMATIC				TAPE	
		Heads for 626	Heads for 69015	Jaws for 68068-[]	Dies for 69710-1	Dies for 69875 • Reversed •• Standard	Dies for 68250-1
26-22	69363†	---	---	---	---	68108-1	---
22-18	---	314516-1 679301-1	---	---	---	---	---
22-16	49935†	314516-1 679301-1	---	---	47812	68240-1• 68096-1••	---
16-14	49935†	314517-1 679301-1	---	---	47813	68241-1• 68097-1••	---
14-12	49592†	314518-1 679301-1	---	---	---	90566-1	---
12-10 16-14 H.D.	49935†	679301-1	---	---	47814 (Str. Wire Only)	68242-1• 68338-1••	---
	49965† (Flag Only)						
8	69339‡ (Str. Wire)	1338757-1	49956	68135	---	68243-1 (Single Indent)	68312-1 (Single Indent)
	69355‡		48412 (Flag Terminals)				
6	59083‡ (No Ratchet)	1338758-1	48172	68136	---	---	68313-1 (Single Indent)
			48413 (Flag Terminals)				
4	---	---	48173	---	---	---	---
2	---	---	48174	---	---	---	---
			48415 (Flag Terminals)				
1/0	---	---	48183	---	---	---	---

AMPOWER* Terminals and Splices



Terminal



Quick Disconnect



Parallel Splice



Butt Splice


Pressure Type Wire Connector Chart (Use Type "C" Tooling)

WIRE SIZE RANGE	UL 424C LISTED	SP LR 7189 CERTIFIED
6 thru 1000 MCM	6 thru 1000 MCM Stranded	6 thru 1000 MCM Stranded


WIRE SIZE	HYDRAULIC TOOLING (Use Power Unit 69120-[] or 314979-1 †Quick Disconnect Terminals Only)				
	Dies for 69099 1752868-1	Dies for 69082 1752786-1	Dies for 69065 59973-1	Dies for 58445-1 1752788-1	Dies for 68073-2
6	69133-1	---	---	---	---
4	69134-2	---	---	---	---
2	46765-3	---	46321-3	---	---
1/0	46766-2	---	46322-2	---	---
	68361-1 †(with locator)				
2/0	46767-2	---	46323-2	---	---
	68253-1 †(with locator)				
3/0	46749-2	---	46324-2	---	---
	59867-1 †(with locator)				
4/0	46750-2	---	46325-2	---	---
	68304-1 †(with locator)				
250 MCM	46751-2 68203-1†	---	---	46326-2	---
300 MCM	46752-2	---	---	---	---
400 MCM	46753-2	69653 68204-1†	---	---	---
500 MCM	---	46755-2 68206-1†	---	---	---
600 MCM	---	46756-2	---	---	---
600 H.D.	---	59870-1	---	---	---
700 MCM	---	46757-2	---	---	---
800 MCM	---	46758-2	---	---	---
900 MCM	---	46759-2	---	---	---
1000 MCM	---	46760-2	---	---	---
1250 MCM	---	---	---	---	68114-1
1500 MCM	---	---	---	---	68282-1

TOOLING AND ACCESSORIES

Hydraulic Crimping Heads



58445-1
1752788-1




69065




69097



69082
1752786-1



69067



68073-2




69069



69099
1752868-1

Hand Tools



Long and
Short Handle




69710-1



Heavy Head


TOOLING AND ACCESSORIES

Hydraulic




DYNA-CRIMP*
Hydraulic Power Units
69120-1 (115 VAC - 60 Hz)
1804700-1 (115 VAC - 60 Hz)
69120-2 (230 VAC - 60 Hz)
1804700-2 (230 VAC - 60 Hz)

Handle Control W/Hose and
Cord 59907-[] and 1901775-[]



Foot Control
68284-1




Hose Assy W/Crimping
Head Coupling




3-Way
Multidirectional
Valve

59220 (No Safety Sw)
59220-2 (W/Safety Sw)



Hand-Operated
Hydraulic Pump
314979-1
1583661-1

59909-[]
1583662-[]




Hand Tool
59975-1




Hand Tool
59973-1

Tape Machines



AMP-TAPETRONIC*
Machine
68250-1




AMP-TAPETRONIC*
Machine
69875



Pneumatic



69015



68068

REVISION SUMMARY:

Corrected die part number for hydraulic tooling in table on page 1.