


Male



Female

Actual

Refer to page 149 for actual size of the terminal.
(except for FVDGM2-5 & CVDGF2-5)

File No.: E42024 LR20812

	Applicable Wire AWG#(mm²)	Part No.	Standard	Dimensions mm (in.)						Color	Tool No.						Qty/box
				ø d	L	E	ø D	ℓ	Material Thickness		YNT-2216	YNT-1614	YA-1	YA-2	YA-4	BCT-0514	
MALE	22 to 16 (0.25 to 1.65)	FVDGM1.25-5		3.96 (.156)	20.2 (.795)	8.7 (.343)	3.5 (.138)	9.5 (.374)	0.4 (.016)	Red	0		0	0	0	0	1,000
	16 to 14 (1.04 to 2.63)	FVDGM2 -5		3.96 (.156)	20.2 (.795)	8.7 (.343)	4.3 (.169)	9.5 (.374)	0.4 (.016)	Blue		0	0	0	0	0	1,000
		FVDGM2 -7		4.95 (.195)	20.7 (.815)	8.7 (.343)	4.3 (.169)	9.5 (.374)	0.4 (.016)								
FEMALE	22 to 16 (0.25 to 1.65)	CVDGF1.25-5		3.96 (.156)	24.0 (.945)	14.0 (.551)	2.7 (.106)	10.0 (.394)	0.4 (.016)	Red	0		0	0	0	0	500
	16 to 14 (1.04 to 2.63)	CVDGF2 -5		3.96 (.156)	25.0 (.984)	14.0 (.551)	3.2 (.126)	11.0 (.433)	0.4 (.016)	Blue		0	0	0	0	0	500
		CVDGF2 -7		4.95 (.195)	25.0 (.984)	14.0 (.551)	3.2 (.126)	11.0 (.433)	0.4 (.016)								

Note:1) Delivery lead times may vary depending on the product. Contact JST for details.