





COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



RoHS compliant

3	12	Signal contact	S0 / Brass	AuroPur / AWG 20
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +130°C)	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

				Measurement without tolerance acc. to ISO 2768-m	SCALE 2:1	TITLE D-Sub Mixed-Layout Connector	
				NAME / DATE			
			DRAWN	sschref 09-04-2014			
			CHECKED	sschref 09-04-2014			
						DWG.NO.	REV.
1				a molex company		FM17W5SA-K121	1
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE		REPLACEMENT FOR:		PAGES 1