

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200790232](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
Series [120079](#)
Connector End A Ultra-Lock (M12)
Connector End B Pigtail
IP Rating IP69K
Material - Contact Copper Alloy
Overview [Brad Ultra-Lock Connection System](#)
Product Name Ultra-Lock (M12)
Protocol EtherNet
Region America
Type Single Ended
UPC 78678884752

Physical

Cable Diameter 5.33mm (.210")
Cable Length 2.0m (6.56')
Color - Cable Jacket Yellow
Coupling Style Push to Lock
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 4
Temperature Range - Operating -25°C to +90°C
Wire Size AWG 22
Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number W04001A09M020

Reference - Drawing Numbers

Sales Drawing SD-120079-011



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120079](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION