


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 10A/125VAC, 6A/250VAC
- Contact Resistance: 50m Ω Max
- Insulation Resistance: 500VDC 100M Ω min.
- Dielectric Strength: 1500VAC for 1 minute

Materials:

- Frames: Nylon (UL flame 94V-2)
- Terminals: Silver plated brass
- Illuminated Actuators: Molded in PC

Mouser Stock No.	Button
103-R13-135B2-02R	Red spot illuminated / neon
103-R13-135B2-02G	Green spot illuminated / neon

Illuminated Rocker Switches

103-R13-135B2-02R, 103-R13-135B2-02G

Mountain Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-R13-135B2-02R](#)