



340

Single Input K-Type Thermocouple Thermometer

Specifications

Measurement Range (K-Type): -40°F to 1200°F (-40°C to 650°C)

Accuracy: $\pm(1\% \text{ of reading} + 4^\circ\text{F})$

Resolution: 0.1° / 1°

Connector Type: Submini

Features

- Single button operation
- Auto Resolution (0.1° / 1°)
- °C/°F Selectable (Switch in battery compartment)
- Auto Off
- Protective rubber boot
- Easy to read LCD display

Dimensions

Size: 1.6" x 6" x 3" (41mm x 152mm x 77mm)

Weight: 9.8oz. (278g)

Size and weight include A304 protective boot

Copyright © 2008 Test Products International, Inc.

