





D

D



1 RCPT CONNECTOR
INSERTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
SHELLS: STEEL PER ASTM A109, PLATED, .000200 MIN TIN OVER .000100 MIN COPPER UNDERPLATE.



C

C

B

B

- 1 RCPT ACCEPTS SIZE 20 SOCKET CONTACTS (CONTACTS MUST BE ORDERED SEPARATELY).
2. ALL PARTS SHIPPED UNASSEMBLED, EACH PART INDIVIDUALLY BULK PACKED.
- 3 SHIELDS: MATERIAL—.020 THICK STEEL, PER ASTM A109, PLATED .000200 MIN TIN OVER .000100 MIN COPPER UNDERPLATE.
- 4 RAISED CAVITY IDENTIFICATION AND AMP TRADEMARK.

1658649-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.REITZEL 31JUL03		 TE Connectivity			
		CHK S.BOLASH 31JUL03					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.WALMSLEY 31JUL03		NAME	
		0 PLC ± -		PRODUCT SPEC		KIT, RCPT, SHIELDING HARDWARE, SIZE 3, 25 ^M POSITION, AMPLIMITE HDP-20	
		1 PLC ± -		108-40030			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± .005		114-40030		SIZE	
		4 PLC ± -		WEIGHT		CAGE CODE	
		ANGLES ± 0° 30'		—		DRAWING NO	
MATERIAL		FINISH		A2 00779		RESTRICTED TO	
SEE CALL OUT 		SEE CALL OUT 		C-1658649		—	
CUSTOMER DRAWING				SCALE		SHEET	
				4:1		1 of 1	
						REV	
						A	

1658649