

- Replacement for PAR16 high voltage 35 W Halogen lamp
- High colour rendering index at $\geq Ra95$
- Up to 80% energy saving
- Dimmable
- Lifetime of 25,000 hrs
- For accent lighting; ideal for spotlighting of various objects in shops, museums, restaurants or along the corridor



Order Code 52040

General Data

Lamp Socket GU10
Design Lens

Geometric Data

Length (mm) 63
Diameter (mm) 50
Weight (g) 85


Electric Data


Wattage (W) 6
Voltage (V) 220-240
Power Factor ≥ 0.75
Operating Frequency (Hz) 50-60 Hz

Photometric Data

Luminous Flux (lm) 220
CRI ≥ 95
CCT 2700 K –warm white
Luminous Intensity (cd) 570
Beam Angle (°) 30°
Lifetime 25,000 hrs

Equivalent to (W) 35 W





Order Code

52040

Product Description

LED PAR16 GU10 6W 2700K WW 220LM DIM

Technical Packaging Details

Barcode	023942520405
EAN 128	(02)00023942520405(37)90(91)53
EAN 14	50023942520400
Pack Dimensions (HxWxL)	79 mm x 57 mm x 57 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	309 mm x 368 mm x 278 mm
Cartons/Layer	8
Layers/Pallet	3
Units/Pallet	2160

Photometric Diagram

52040

