






|                                                      |                                                                               |
|------------------------------------------------------|-------------------------------------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 734-338                                                                       |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 1.5                                                                    |
| Cross section2 (Cross section / AWG)                 | 28 - 14                                                                       |
| Strip length (Strip length / mm)                     | 6 - 7                                                                         |
| Measured voltage (Measured voltage / V)              | 160                                                                           |
| Measured shock voltage (Measured shock voltage / kV) | 2.5                                                                           |
| Pollution degree (Pollution degree)                  | 2                                                                             |
| Current intensity (Current intensity / A)            | 10                                                                            |
| RM (PIN SPACING / mm)                                | 3.81                                                                          |
| P (NO. OF POLES)                                     | 8                                                                             |
| Height (Height / mm)                                 | 13.4                                                                          |
| Width (Width / mm)                                   | 32.57                                                                         |
| Depth (Depth / mm)                                   | 22.3                                                                          |
| No. of connection Points (No. of connection Points)  | 8                                                                             |
| No. of potentials (No. of potentials)                | 8                                                                             |
| COLOR (COLOR)                                        | orange                                                                        |
| Comment (Comment)                                    | L = (No. of poles - 1) x Pin Spacing + 5,9 mm<br>+ 0,45 mm   L1 = L - 0,45 mm |