

**Wire Connectors & Termination****T&B Catalog Number:**

10-411

UPC Number:

78378610411

Status:

Active

Description:

Multi-Carton packed high temperature porcelain wire connector, HI-1.

Features

Three sizes accommodate #18-14AWG stranded
Copper
300 Volt rated.

Application

For high temperature applications over 105 degree
C

General

Wire Range #18-14
Minimum 2 #18
Maximum 1 #18 w/2 #16

Dimension Information

Dimension A (inches) 11/16
Dimension B (inches) 13/32
Dimension C (inches) 3/16
Dimension D (inches) 1/4

Packaging

T&B Order Multiple 1000
Package in Units 1000
T&B Sold in UOM Each
T&B Weight Per UOM 0.37 lbs. per 100

Application Support

Product Overview Available on Website

Notes

Wire range size applies to stranded only.

Certifications

RoHS Compliance Yes

Certifications

File Nbr:

E 9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com