


Part Number: 53798-1924

Image not available

Status: Inactive
Series: [53798](#)
Category: Backplane Connectors

Series image - Reference only

Mates With Part(s):
[54613](#), [54526](#), [54867](#), [59232](#)

Part Detail
General

Status	Inactive
Category	Backplane Connectors
Series	53798
Application	Backplane
Component Type	PCB Header
Product Name	MFB™
Style	N/A

Physical

Circuits (Loaded)	192
Circuits (maximum)	192
Durability (mating cycles max)	250
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Number of Columns	N/A
Number of Pairs	Open Pin Field
Number of Rows	4
Orientation	Vertical
PC Tail Length	17.00mm
PCB Retention	None
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Stackable	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Data Rate	622.0 Mbps
Voltage - Maximum	100V AC

Material Info

UPC	800753923720
-----	--------------

Reference - Drawing Numbers

Product Specification	RPS-54047-004
Sales Drawing	SD-53798-***4

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application
Tooling

[Check our list of old tooling that used to be available for this part](#)