


Low Voltage DC Power Plug

171-MP214-E

KOBI CONN

Low Voltage DC Power Plug



Dimensions: mm (IN.)

SPECIFICATIONS

Mates With:	163-510DJ-E
Rating:	13.5VDC 2A
Dielectric Strength:	500VAC for 1 Minute
Insulation Resistance:	100MQ min. @ 500VDC
RoHS Compliant	

No.	Part Name	Material	Finish
1	Outer Contact	BSBM	NI
2	Insulator A	POM	---
3	Center Contact	BSBM	NI
4	Outer Terminal	SI	NI
5	Insulator B	Phoenol	---
6	Center Terminal	SI	NI
7	Handle	PE	---

Date Last Revised: 12-9-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300913

171-MP214-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-MP214-E](#)