


REV	DOCUMENT	CHANGED BY	CHECK
7	0060324	VKR 13JAN10	CMH



RELEASE NO.	PR-16094
REPLACES	X87835-SX

CHARACTERISTICS	ELECTRICAL DATA	DESIGN UNITS: INCH	DRAWN	VK	05 MAR 08	Honeywell			
OPERATING FORCE - - - - 5 OZ MAX	CONTACT ARRANGEMENT S P D T	TOLERANCES UNLESS NOTED:	CHECK	RJ	05 MAR 08				
RELEASE FORCE - - - - 1 OZ MIN	28 VOLTS DC RATING	NO PLACE X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
	SEA LEVEL	ONE PLACE .X ± .030							
DIFFERENTIAL TRAVEL - - - .003 MAX	INDUCTIVE 0.5 AMP	TWO PLACE .XX ± .015							
OVERTRAVEL - - - - - .003 MIN	RESISTIVE 1.0 AMP	THREE PLACE .XXX ± .005							
		FOUR PLACE .XXXX ±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
		ANGLES ±	RASTER			B	I	12SX15-T	7
		THIRD ANGLE PROJECTION 				SCALE	-	WEIGHT .003 LB MAX	SHEET 1 OF 1