


RJ45 Hybrid Cable, Cat5, PUR
4AWG 26/7, 3AWG 20/7



- Transmission properties in accordance with ISO/IEC 11801:2002, EN 50 173-1: Class D.
- Protection level: IP67/65
- Temperature range: -40°C ...+70°C


For Information Only
-won't be replaced when changed-

Loading-Plan Power wires

red	1
brown	2
yellow	3

Data wires Shield

blue	4
white	5
orange	6
yellow	7



7	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 200	20 m
6	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 100	10 m
5	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 050	5 m
4	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 030	3 m
3	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 020	2 m
2	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 010	1 m
1	Hybrid Cable, 4AWG 26/7, 3AWG 20/7	09 47 61 00 005	0,5 m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2:1	RJ1 cord, 1xPush Pull Hybrid 4AWG26/7+3AWG20/7, CAT5				
			Detail.	30.07.08	MS						
			Insp.								
			Stand.								
35006			HARTING Electronics GmbH & Co. KG				TB 09 47 61 00 xxx				
Mod.	Dat.	Name	D-32339 ESPELKAMP								
							Blatt/ page /				