

## D-SUB CONNECTOR CONTACTS



✓ Active

### TE CONNECTIVITY (TE) SOCKET ASSY SZ 20 AMPLIMITE

206795-1  
TE Internal Number: 206795-1

EU RoHS Compliant with Exemptions  
EU ELV Compliant with Exemptions  
Contact Type Socket  
Contact Style Crimp Snap-in  
Contact Size 20  
Contact Base Material Copper Alloy  
Contact Mating Area Plating Material Gold

 **PRODUCT DRAWING**  
English

 **3D PDF**

### DOCUMENTATION

Product Drawings

#### **SOCKET CONTACT ASSY,SIZE 20 (FOR #26 & #28 WIRE)**

PDF

English

CAD Files

#### **3D PDF**

PDF

3D

#### **Customer View Model**

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Application Specification

## Size VIII Power Contacts

PDF

English

---

Instruction Sheets

Instruction Sheet (U.S.)

## Application Tooling For Screw-Machine Contacts

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Connector & Contact Terminates To** Wire & Cable

**Product Type** Contact

---

Contact Features

**Contact Type** Socket

**Contact Style** Crimp Snap-in

**Contact Size** 20

**Contact Base Material** Copper Alloy

**Contact Mating Area Plating Material** Gold

**Pin Diameter (mm)** .45

**Contact Mating Area Plating Thickness (µin)** 50

---

Termination Features

**Termination Method to Wire/Cable** Crimp

---

Dimensions

**Post Diameter** .085 mm [ 2.16 in ]

**Wire Range** .08 – .15 mm<sup>2</sup> [ 28 – 26 AWG ]

**Insulation Diameter (Max)** .072 mm [ 1.83 in ]

---

Operation/Application

High Current No

---

Packaging Features

**Packaging Method** Package  
**Packaging Quantity** 1000

---

## PRODUCT COMPLIANCE



---

Statement of Compliance

### **Statement of Compliance**

PDF

---