

AS6			AS2.5/3			AS2.5/4			AS4/3		
											
											
8 mm			5 mm			5 mm			6 mm		
48 x 74 mm			42 x 54 mm			42 x 54 mm			42 x 61.5 mm		
15 mm			11 mm			11 mm			15 mm		
Polyamide 6.6			Polyamide 6.6			Polyamide 6.6			Polyamide 6.6		
2 spring clamps & 2 slots for interconnection			3 spring clamps & 2 slots for interconnection			4 spring clamp connection			3 spring clamps & 2 slots for interconnection		
											
22-8 AWG	0.2-6 sq.mm.	22-8 AWG	22-12 AWG	0.34-2.5 sq.mm	22-12 AWG	22-12 AWG	0.34-2.5 sq.mm	22-12 AWG	22-10 AWG	0.2-4 sq.mm.	22-10 AWG
600 V	800 V	600 V	600V	800 V	600 V	600V	800 V	600 V	600 V	800 V	600 V
50 A	41 A	50 A	25A	24 A	25 A	25 A	24 A	25 A	35 A	32 A	35 A
   			   			   			   		
Cat. No.		Std. Pk.	Cat. No.		Std. Pk.	Cat. No.		Std. Pk.	Cat. No.		Std. Pk.
AS6		50	AS2.5/3		100	AS2.5/4		100	AS4/3		100
EPAS6		50	EPAS2.5		50	EPAS2.5		50	EPAS4		50
 			 			 			 		
CA103	50		CA103	50		CA103	50		CA103	50	
CA702	50		CA702	50		CA702	50		CA702	50	
CA802	50		CA802	50		CA802	50		CA802	50	
CA801/3		100	CA801/1		100	DOES NOT ACCEPT JUMPERS			CA801/2		100
CA801/3-3		100	CA801/1-3		100				CA801/2-3		100
CA901/3		100	CA901/1		100				CA901/2		100
CA901/4		100	CA901/5		100				CA901/4		100
CA901/5		100	CA901/6		100				CA901/5		100
MT8		100	MT5		100	MT5		100	MT6		100