

Specifications:

Resonant Frequency (Hz)	4100 ± 500
Operating Voltage (Vdc)	3 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	10 at Rated Voltage
Sound Pressure Level Min. (dB)	83 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Housing	PBT (Color: Black)
Leading Pins	Tin Plated Brass
Weight (Grams)	1.0
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant
