

20

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.




THIS DRAWING IS UNPUBLISHED.

BY -


COPYRIGHT 20

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	L2	REDRAWN AND REV. BY ECO16-005813	30JUN2016	HC	WLS



SECTION A - A



SECTION B - B

① - REELED WITH PAPER INTERLEAVE

② - $\varnothing 4,3$ mm. FOR M4 HOLE.
 3-FOR STD CABLE: INS.
 CRIMPER "F" ($\varnothing 1,78-3,06$ mm.)
 FOR THIN WALL CABLE INS.
 CRIMPER "OV" ($\varnothing 1,3-1,6$ mm)

OBSOLETE

TIN-PLATED	BRASS	626028-4	①
	PH. BRONZE	626028-3	
TIN-PLATED	BRASS	626028-2	
—	BRASS	626028-1	
FINISH	MATERIAL	PART NUMBER	

WIRE RANGE 0,5-1,5mm²INSUL. RANGE $\varnothing 1,8-3,0$ mm

DIMENSIONS:

mm

DWN 30JUN2016

H.C. CANTERI

CHK 30JUN2016

W.L. STEFANI

APVD -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

MATERIAL

SEE TABLE

FINISH

SEE TABLE

TE

TE Connectivity

NAME RING TONGUE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

-

C-626028

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

OF

REV

L2