

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0676431091

Status:

Obsolete

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Type A, White Polyester, 0.76µm (30µ") Gold (Au) Plating, PCB Thickness 1.60mm (.063"), with Upper Flange




image - Reference only

Series

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

67643Series

Mates With

USB Type A Plug

General

Product Family	I/O Connectors
Series	67643
Application	Wire-to-Board
Comments	With Upper Flange Not for IR Reflow Process
Component Type	Receptacle
Product Name	USB
Type	A

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Right Angle
PC Tail Length	2.60mm (.102")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.50mm (.098")
Plating min - Mating	0.762µm (30µ")
Polarized to Mating Part	Yes
Temperature Range - Operating	0°C to +50°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Product Specification	PS-67998-0000
-----------------------	---------------

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION