

.050" (1,27mm) CABLE STRIPS FFSD, FFMD SERIES

SPECIFICATIONS

FFSD Mates with:
FTS, FTSH, EHF,
SHF, ESHF

For complete specifications
see www.samtec.com?FFSD

FFSD

Insulator Material:
PBT

Contact:

BeCu
Plating:
10µ" (0,25µm) Au over 50µ"
(1,27µm) Ni on contact area;
Sn over 50µ" (1,27µm) Ni
on balance

Wire:

30 AWG
Current Rating:
0.5A

Operating Temp Range:
-40°C to +105°C

Lead Size Accepted:
(0,41mm) .016" SQ

Contact Resistance:
10 mΩ maximum

Insertion Depth:
(2,64mm) .104" to
(3,17mm) .125"

Insertion Force:
(Single contact only)

5oz (1,39N) avg.

Withdrawal Force:
(Single contact only)

3oz (0,83N) avg.

ROHS Compliant:
Yes

Note: This Series is
non-standard, non-returnable.

SPECIFICATIONS

Mates with:
FLE*, SFMC*

For complete specifications
see www.samtec.com?FFMD

FFMD

Insulator Material:
Black Glass Filled

Polyester

Terminal: BeCu

Plating:
Sn over 50µ" (1,27µm) Ni

Wire: 30 AWG

Current Rating: 0.5A

Operating Temp Range:
-40°C to +105°C

ROHS Compliant: Yes


***Note:** Standard FFMD callout
will not mate with FLE, SFMC.
Must use gold plated callouts.
See drawing on web.

Note: This Series is
non-standard, non-returnable.

TYPE STRIP — **NO. PINS PER ROW** — **END OPTION** — **OVERALL LENGTH** — **01** — **OPTION** — **OTHER OPTION**

—05, —08 —10, —13,
—17, —20, —25
(Call for other sizes)


—“XX.XX”
= Assembled Length




—N
= Notch
Polarization
(FFSD only)

Leave blank
for —S and —D
End Options.
For —T End Option
Specify “—N”
(Socket has
notch polarization)
(FFMD only)


—S = Single End




—D = Double End



—T = Transfer End
(FFMD only)




—RW = Reverse
Wiring




Blue or black wire
opposite position #1.


—D “XX” = Daisy
Chain




—R = Reverse




—M = Middle
Reverse



—O = Outside
Reverse



—SR = Strain
Relief




No. of positions x
(1,27) .050 + (8,00) .315




Not available with —S,
—O, —M, —R or —DXX

FFSD = Socket Strip



FFMD = Terminal Strip



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047

SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299

SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413

SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340

SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520

SAMTEC FRANCE • Tel: 33 01 60 95 06 60 • Fax: 33 01 60 95 06 61

SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690

SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575

SAMTEC UK • Tel: 44 01236 739292 • Fax: 44 01236 727113

SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315

SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187

SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036

SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502

SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842

SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681

SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112 • Fax: 27 86 6714432

SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745