


Dimensions: mm (In.)

Date Last Revised: 10-20-05



Tolerance 0.3 (.012) except noted.

SPECIFICATIONS

Rating:	20A 24VDC
Contact Resistance:	50m Ω max.
Insulation Resistance:	500VDC 100M Ω min.
Dielectric Strength:	1500VAC, 1 minute
Contacts:	Copper Alloy Tin Plated
Body:	Nylon #66

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-R352](#)