TE-type Twin Wheel Caster

■Characteristic

Double wheel mechanism.
Outer wheel made of elastomer gives little damage and stains on the floor, and its running sounds are very quiet.
New stopper is applied to obtain better operability.
Stop both swivel and turn which is suitable for vibration machines.

■Application

Medical instruments /
Office automation appliances /
Audio racks / Television stands /
Wagons

Part Name	Material
Main Body	PA
Inner Wheel	
Outer Wheel	Elastomer

■Specification

Model No.	Type		Allowable Load(kg)	Code No.
	Shape	Stopper		
TE50	Plate type	—	50	19001
TE50S		With stopper		19006
TE50N3	Screw type	—		19002
TE50N3S		With stopper		19007
TE50N8		—		19003
TE50N8S		With stopper		19008
TE50N10		—		19004
TE50N10S		With stopper		19009
TE50N12		—		19005
TE50N12S		With stopper		19010
TE130N16		—	140	19064
TE130N16WS		With double stopper		19065

■Size List Plate type

Model No.	A	B	C	D	E	G	H1	J1	W1	W2
TE50･TE50S	49	ϕ40	ϕ54	ϕ50	17	ϕ5.5	65	t3	49	21

※Dimension A shows caster with stopper only.

Plate type





This drawing shows caster with stopper.

Screw type





This drawing shows caster with stopper.

■Size List Screw type

Model No.	A	D	E	d	H2	J2	K	L	W1	W2
TE50N3 -N3S	49	ϕ50	17	W3/8—16	57.5	t6	17	19	49	21
TE50N8 -N8S				M8×1.25				14		
TE50N10 -N10S				M10×1.5						
TE50N12 -N12S				M12×1.75						
TE130N16-N16WS	110	ϕ130	35	M16×2.0	145	t8	21	25	70.2	29

※Dimension A shows caster with stopper only.