






# FEMALE PLUG PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING 713-1103 TO 713-1118

|                                                      |                                                   |
|------------------------------------------------------|---------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 713-1115                                          |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 1.5                                        |
| Cross section2 (Cross section / AWG)                 | 28 - 16                                           |
| Strip length (Strip length / mm)                     | 6 - 7                                             |
| Measured voltage (Measured voltage / V)              | 160                                               |
| Measured shock voltage (Measured shock voltage / kV) | 2.5                                               |
| Pollution degree (Pollution degree)                  | 2                                                 |
| Current intensity (Current intensity / A)            | 10                                                |
| RM (PIN SPACING / mm)                                | 3.5                                               |
| P (NO. OF POLES)                                     | 30                                                |
| Height (Height / mm)                                 | 18.8                                              |
| Width (Width / mm)                                   | 54                                                |
| Depth (Depth / mm)                                   | 16                                                |
| No. of connection Points (No. of connection Points)  | 30                                                |
| No. of potentials (No. of potentials)                | 30                                                |
| COLOR (COLOR)                                        | schwarz                                           |
| Comment (Comment)                                    | L = ((No. of poles / 2) - 1) x Pin Spacing + 5 mm |