

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

RoHS

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Flash Gold

Contact Material: Phosphor bronze

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.


Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSIONS	
	A	B
06	2.54	8.00
08	3.81	9.27
10	5.08	10.54
12	6.35	11.81
14	7.62	13.08
16	8.89	14.35
20	11.43	16.89
24	13.97	19.43
26	15.24	20.70
30	17.78	23.24
34	20.32	25.78
40	24.13	29.59
44	26.67	32.13
50	30.48	35.94
60	36.83	42.29
64	39.37	44.83
66	40.64	46.10
68	41.91	47.37
70	43.18	48.64
74	45.72	51.18
76	46.99	52.45
80	49.53	54.99

MATING PART



UNLESS TOLERANCE		DRAW BY		Cnc Tech,LLC	
GENERAL	ANGLE	DESIGN BY			
X. ± 0.30	X.° ± 3.0°	CHECK BY			
.X ± 0.20	.X° ± 2.0°				
.XX ± 0.15	.XX° ± 1.0°	APPROVE BY		Part NO. 3230-XX-0101-00	
.XXX ± 0.10	.XXX ± 0.5°				
SCALE		SHEET	UNIT	DRAW NO:	
1:1		1/1	MM		
REV: A					