



D±0.08 DIA
[±.003]
4 HOLES



23	3.81[.150]	38.35[1.510]	44.45[1.750]	36.53[1.438]	207299-4
17	3.81[.150]	28.19[1.110]	36.45[1.435]	28.58[1.125]	207299-3
13	3.18[.125]	22.22[.875]	32.51[1.280]	24.61[.969]	207299-2
11	3.18[.125]	19.05[.750]	28.58[1.125]	21.44[.844]	207299-1
SIZE	D	C	B	A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM[INCHES]

MATERIAL
NYLON, BLACK

FINISH
—

0 PLC ± —
1 PLC ± —
2 PLC ± 0.13 [.005]
3 PLC ± —
4 PLC ± —
ANGLES ± —

DWN
D.HARDY
05/20/94
CHK
R.STONE
05/20/94
APVD
A.FRANTUM
07/13/94

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
—

TE Connectivity

FLANGE, PLUG, CPC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-207299

RESTRICTED TO
—

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

CUSTOMER DRAWING

SCALE
2:1

SHEET
1 of 1

REV
A1

1470-19 (3/11)