









6. PRODUCT COMPLIANT TO RoHS DIRECTIVE 2011/65/EU AND ELV DIRECTIVE 2000/53/EC.



RECOMMENDED PANEL CUT OUT DIMENSION

REVISE NOTE EC NO: S2014-0536 DRAWN:CS00 CHKD: JANO2 APPR:KHLIM	2013/12/05	DESCRIPTION	QUALITY SYMBOLS F = 0 F = 0 F = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
	2013/12/10			mm INCH	DRAWN BY RZHANG DATE 2004/07/20	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex					
	2013/12/17			4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.25 ± ---	CHECKED BY GRMA DATE 2004/07/20						
	2013/12/20			1 PLACE ± 0.25 ± --- 0 PLACE ± ±	APPROVED BY YTYAP DATE 2004/07/20						
				ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 6		SD-47151-001		1 OF 8	
	1	REV		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO SHEET 1.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC00 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
						MM ONLY		NTS	METRIC				
								TITLE					
L1		REV	QUALITY SYMBOLS			DRAWN BY DATE		1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE					
						MM ONLY							
								CHECKED BY DATE		molex			
								APPROVED BY DATE					
				ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 6		SD-47151-001		2 OF 8			
						SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10

9

8

7

6

5








4

3

2

1

WITH BACK COVER



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0001.
2. PACKAGE SPECIFICATION FOR WITHOUT FLANGE REFER TO PK-47151-001.

REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FCS00 CHKD:JAN02 APPR:KHLIM 2013/12/20	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION SITS ONLY FOR 47151-1061/1071/1081 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex
				mm	INCH	DRAWN BY RZHANG	DATE THIS SHEET ONLY 2004/07/20		
			4 PLACES	± ---	± ---	CHECKED BY GRMA	DATE 2004/07/20		
			3 PLACES	± ---	± ---	APPROVED BY YTYAP	DATE 2004/07/20		
			2 PLACES	± 0.25	± ---				
1 PLACE	± 0.25	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
L1			ANGULAR ± 3 °		SEE SHEET 6		SD-47151-001		3 OF 8
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9

8

7

6

5

4








3

2

1

10 9 8 7 6 5 4 3 2 1

WITH BACK COVER



THIS IS ONLY FOR
47151-1025/1075/1085/6022/6032/1026/2062

- NOTES:
1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-0002.
 2. PACKAGE SPECIFICATION FOR WITH FLANGE:
OPTION 1: 47151-1026/2062/6032 REFER TO PK-47151-005,
OPTION 2: 47151-1102 REFER TO PK-47151-003,
OPTION 3: OTHER PART NUMBER REFER TO PK-47151-002.

REVISE NOTE EC NO: S2014-0536 DRW:NFC000 CHKD: JIAN02 APP: KHLIM	2013/12/05 2013/12/17 2013/12/20	DESCRIPTION REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
					mm	INCH	DRAWN BY RZHANG	DATE 2004/07/20	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE molex						
				4 PLACES	± ---	± ---	CHECKED BY GRMA	DATE 2004/07/20							
				3 PLACES	± ---	± ---	APPROVED BY YTYAP	DATE 2004/07/20							
				2 PLACES	± 0.25	± ---	MATERIAL NO.							DOCUMENT NO.	SHEET NO.
				1 PLACE	± 0.25	± ---	SEE SHEET 6							SD-47151-001	4 OF 8
				0 PLACE	±	±	SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
				ANGULAR ± 3 °											
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											

9 8 7 6 5 4 3 2 1

10

9

8

7

6


5

4





3

2

1



WITHOUT TOP HOLE



NOTES:

1. THE UNSPECIFIED DIMENSIONS REFER TO 47151-1102.
2. PACKAGE SPECIFICATION FOR WITH FLANGE REFER TO PK-47151-002.

REV	DESCRIPTION	DATE	BY
L1	REVISE NOTE	2013/12/05	EC NO: S2014-0536
		2013/12/17	DRWN:CS00
		2013/12/17	CHKD:JTAN02
		2013/12/20	APPR:KHLIM

QUALITY SYMBOLS
$\nabla_A = 0$
$\nabla_C = 0$
$\nabla_D = 0$

GENERAL TOLERANCES (UNLESS SPECIFIED)	
4 PLACES	± 0.25
3 PLACES	± 0.25
2 PLACES	± 0.25
1 PLACE	± 0.25
0 PLACE	± 0.25
ANGULAR $\pm 3^\circ$	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20
MATERIAL NO.	
SEE SHEET 6	

SCALE	DESIGN UNITS		THIRD ANGLE
NTS	METRIC		PROJECTION
TITLE			
1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE			
molex			
DOCUMENT NO.		SHEET NO.	
SD-47151-001		5 OF 8	
TAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

9

8

7

6

5

4

3

2

1

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																													
F	<table><tr><th rowspan="2">ASSEMBLY P/N</th><th colspan="5">DIMENSION</th><th colspan="4">FEATURE</th><th rowspan="2">HOUSING COLOUR</th><th rowspan="2">GOLD PLATING IN CONACT AREA</th><th rowspan="2">SHELL PLATING</th><th rowspan="2">REMARK</th></tr><tr><th>DIM A</th><th>DIM B</th><th>DIM C</th><th>DIM D</th><th>DIM E</th><th>FLANGE</th><th>BACK COVER</th><th>TOP HOLES</th><th>MYLAR</th></tr><tr><td>47151-0001</td><td rowspan="7">1.80</td><td rowspan="7">2.20</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">W/O</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td><td rowspan="14">FOR SHEET 1</td></tr><tr><td>47151-0041</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0051</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0011</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0071</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0061</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0021</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0031</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-0101</td><td rowspan="7">1.45</td><td rowspan="7">1.45</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">/</td><td rowspan="7">W/O</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td></tr><tr><td>47151-0141</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0151</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0111</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0181</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0161</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0121</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0131</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-0002</td><td rowspan="7">1.80</td><td rowspan="7">2.20</td><td rowspan="7">M3.0X0.5</td><td rowspan="7">16.08</td><td rowspan="7">13.38</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td><td rowspan="14">FOR SHEET 2</td></tr><tr><td>47151-0042</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0062</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0012</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0052</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0072</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0022</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0032</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-0102</td><td rowspan="7">1.45</td><td rowspan="7">1.45</td><td rowspan="7">M3.0X0.5</td><td rowspan="7">16.08</td><td rowspan="7">13.38</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td rowspan="7">WITH</td><td rowspan="7">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="7">SEE NOTE 2 (a)</td></tr><tr><td>47151-0142</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0162</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0112</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0152</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-0172</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-0122</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-0132</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-6002</td><td rowspan="4">1.80</td><td rowspan="4">2.20</td><td rowspan="4">M3.0X0.5</td><td rowspan="4">14.25</td><td rowspan="4">11.28</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td rowspan="4">WITH</td><td rowspan="4">W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="4">SEE NOTE 2 (a)</td></tr><tr><td>47151-6062</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6082</td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6102</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6172</td><td rowspan="2">1.45</td><td rowspan="2">1.45</td><td rowspan="2">M3.0X0.5</td><td rowspan="2">14.25</td><td rowspan="2">11.28</td><td rowspan="2">WITH</td><td rowspan="2">W/O</td><td rowspan="2">WITH</td><td rowspan="2">W/O</td><td>BLACK</td><td>SEE NOTE 2 (2)</td><td rowspan="2"></td></tr><tr><td>47151-6162</td><td>SEE NOTE 2 (3)</td></tr></table>											ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR	47151-0001	1.80	2.20	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 1	47151-0041	SEE NOTE 2 (2)	47151-0051	SEE NOTE 2 (3)	47151-0011	SEE NOTE 2 (1)	47151-0071	SEE NOTE 2 (2)	47151-0061	SEE NOTE 2 (3)	47151-0021	SEE NOTE 2 (1)	47151-0031	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0101	1.45	1.45	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-0141	SEE NOTE 2 (2)	47151-0151	SEE NOTE 2 (3)	47151-0111	SEE NOTE 2 (1)	47151-0181	SEE NOTE 2 (2)	47151-0161	SEE NOTE 2 (3)	47151-0121	SEE NOTE 2 (1)	47151-0131	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 2	47151-0042	SEE NOTE 2 (2)	47151-0062	SEE NOTE 2 (3)	47151-0012	SEE NOTE 2 (1)	47151-0052	SEE NOTE 2 (2)	47151-0072	SEE NOTE 2 (3)	47151-0022	SEE NOTE 2 (1)	47151-0032	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-0102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-0142	SEE NOTE 2 (2)	47151-0162	SEE NOTE 2 (3)	47151-0112	SEE NOTE 2 (1)	47151-0152	SEE NOTE 2 (2)	47151-0172	SEE NOTE 2 (3)	47151-0122	SEE NOTE 2 (1)	47151-0132	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-6002	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-6062	SEE NOTE 2 (2)	47151-6082	SEE NOTE 2 (3)	47151-6102	SEE NOTE 2 (1)	47151-6172	1.45	1.45	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)		47151-6162	SEE NOTE 2 (3)	F
ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA		SHELL PLATING	REMARK																																																																																																																																																																									
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR																																																																																																																																																																														
47151-0001	1.80	2.20	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 1																																																																																																																																																																										
47151-0041										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0051										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0011										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0071										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0061										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0021										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0031	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																					
47151-0101	1.45	1.45	/	/	/	W/O	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																											
47151-0141										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0151										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0111										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0181										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0161										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0121										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0131	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																					
47151-0002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 2																																																																																																																																																																										
47151-0042										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0062										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0012										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0052										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0072										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0022										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0032	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																					
47151-0102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																											
47151-0142										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0162										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0112										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0152										SEE NOTE 2 (2)																																																																																																																																																																													
47151-0172										SEE NOTE 2 (3)																																																																																																																																																																													
47151-0122										SEE NOTE 2 (1)																																																																																																																																																																													
47151-0132	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																					
47151-6002	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																											
47151-6062										SEE NOTE 2 (2)																																																																																																																																																																													
47151-6082										SEE NOTE 2 (3)																																																																																																																																																																													
47151-6102										SEE NOTE 2 (1)																																																																																																																																																																													
47151-6172	1.45	1.45	M3.0X0.5	14.25	11.28	WITH	W/O	WITH	W/O	BLACK	SEE NOTE 2 (2)																																																																																																																																																																												
47151-6162										SEE NOTE 2 (3)																																																																																																																																																																													
E												E																																																																																																																																																																											
D												D																																																																																																																																																																											
C												C																																																																																																																																																																											
B												B																																																																																																																																																																											
A	<table><tr><td rowspan="10">REVISE NOTE EC NO: S2014-0536 2013/12/05 DRW:NFC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20</td><td rowspan="10">QUALITY SYMBOLS F=0 F=0 F=0</td><td rowspan="10">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">mm</td><td colspan="2">INCH</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="10">THIRD ANGLE PROJECTION</td></tr><tr><td colspan="2">4 PLACES ± ---</td><td colspan="2">± ---</td><td>DRAWN BY</td><td>DATE</td><td rowspan="2">TITLE</td></tr><tr><td colspan="2">3 PLACES ± ---</td><td colspan="2">± ---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td colspan="2">2 PLACES ± 0.25</td><td colspan="2">± ---</td><td>GRMA</td><td>2004/07/20</td><td rowspan="2">1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE</td></tr><tr><td colspan="2">1 PLACE ± 0.25</td><td colspan="2">± ---</td><td>APPROVED BY</td><td>DATE</td></tr><tr><td colspan="2">0 PLACE ±</td><td colspan="2">±</td><td>YTYAP</td><td>2004/07/20</td><td rowspan="2">molex</td></tr><tr><td colspan="6">ANGULAR ± 3 °</td><td>MATERIAL NO.</td><td>DOCUMENT NO.</td><td>SHEET NO.</td></tr><tr><td colspan="6">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE SHEET 6</td><td colspan="2">SD-47151-001</td><td>6 OF 8</td></tr><tr><td colspan="6">SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>											REVISE NOTE EC NO: S2014-0536 2013/12/05 DRW:NFC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	mm		INCH		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	4 PLACES ± ---		± ---		DRAWN BY	DATE	TITLE	3 PLACES ± ---		± ---		CHECKED BY	DATE	2 PLACES ± 0.25		± ---		GRMA	2004/07/20	1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE	1 PLACE ± 0.25		± ---		APPROVED BY	DATE	0 PLACE ±		±		YTYAP	2004/07/20	molex	ANGULAR ± 3 °						MATERIAL NO.	DOCUMENT NO.	SHEET NO.	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE SHEET 6		SD-47151-001		6 OF 8	SIZE A3						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					A																																																																																															
REVISE NOTE EC NO: S2014-0536 2013/12/05 DRW:NFC00 CHKD:JTAN02 APPR:KHLIM 2013/12/20	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	mm		INCH		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																																												
			4 PLACES ± ---		± ---		DRAWN BY	DATE	TITLE																																																																																																																																																																														
			3 PLACES ± ---		± ---		CHECKED BY	DATE																																																																																																																																																																															
			2 PLACES ± 0.25		± ---		GRMA	2004/07/20	1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE																																																																																																																																																																														
			1 PLACE ± 0.25		± ---		APPROVED BY	DATE																																																																																																																																																																															
			0 PLACE ±		±		YTYAP	2004/07/20	molex																																																																																																																																																																														
			ANGULAR ± 3 °							MATERIAL NO.					DOCUMENT NO.	SHEET NO.																																																																																																																																																																							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE SHEET 6						SD-47151-001		6 OF 8																																																																																																																																																																						
			SIZE A3						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																														
				fb_frame_A3_P_AM.T Rev. G 2012/01/11	9	8	7	6	5	4		3	2	1																																																																																																																																																																									

F

E

D

C

B

A

F

E

D

C

B

A

ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK	
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR					
47151-1001	1.80	2.20	/	/	/	W/O	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 3	
47151-1041											SEE NOTE 2 (2)			
47151-1051											SEE NOTE 2 (3)			
47151-1003											SEE NOTE 2 (4)			
47151-1061									WITH	BLACK	SEE NOTE 2 (1)			
47151-1071											SEE NOTE 2 (2)			
47151-1081											SEE NOTE 2 (3)			
47151-1011											SEE NOTE 2 (1)			
47151-1211									W/O	NATURE	SEE NOTE 2 (2)			
47151-1311											SEE NOTE 2 (3)			
47151-1021											SEE NOTE 2 (1)			
47151-1091										BLACK	SEE NOTE 2 (3)	SEE NOTE 2 (b)		
47151-1031											SEE NOTE 2 (1)			
47151-1101	1.45	1.45	/	/	/	W/O	WITH	WITH	W/O	SEE NOTE 2 (1)	SEE NOTE 2 (a)			
47151-1141										BLACK		SEE NOTE 2 (2)		
47151-1151												SEE NOTE 2 (3)		
47151-1111												SEE NOTE 2 (1)		
47151-1161										NATURE		SEE NOTE 2 (2)		SEE NOTE 2 (b)
47151-1171												SEE NOTE 2 (3)		
47151-1121											SEE NOTE 2 (1)			
47151-1131										BLACK	SEE NOTE 2 (1)			
47151-7102											NATURE	SEE NOTE 2 (1)		
47151-7142	1.45	1.45	M3.0x0.5	16.08	13.38	WITH	WITH	W/O	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 5	
47151-7162											SEE NOTE 2 (2)			
											SEE NOTE 2 (3)			

REVISE NOTE

EC NO: S2014-0536

2013/12/05

DRWN:FC500

2013/12/17

CHKD:JTAN02

2013/12/20

APPR:KHLIM

2013/12/20

DESCRIPTION

REV

L1

QUALITY SYMBOLS

$\nabla_A=0$

$\nabla_C=0$

$\nabla_P=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.25	± ---
0 PLACE	±	±

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY	DATE
RZHANG	2004/07/20
CHECKED BY	DATE
GRMA	2004/07/20
APPROVED BY	DATE
YTYAP	2004/07/20

MATERIAL NO.

SEE SHEET 6

SIZE

A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

1.0 HDMI RIGHT ANGLE
HEADER ASSEMBLY(19 PIN)
LEAD FREE

molex

DOCUMENT NO.

SD-47151-001

SHEET NO.

7 OF 8

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																											
F	<table><tr><th rowspan="2">ASSEMBLY P/N</th><th colspan="5">DIMENSION</th><th colspan="4">FEATURE</th><th rowspan="2">HOUSING COLOUR</th><th rowspan="2">GOLD PLATING IN CONACT AREA</th><th rowspan="2">SHELL PLATING</th><th rowspan="2">REMARK</th></tr><tr><th>DIM A</th><th>DIM B</th><th>DIM C</th><th>DIM D</th><th>DIM E</th><th>FLANGE</th><th>BACK COVER</th><th>TOP HOLES</th><th>MYLAR</th></tr><tr><td>47151-1002</td><td rowspan="9">1.80</td><td rowspan="9">2.20</td><td rowspan="9">M3.0X0.5</td><td rowspan="9">16.08</td><td rowspan="9">13.38</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td>W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="9">SEE NOTE 2 (a)</td><td rowspan="37">FOR SHEET 4</td></tr><tr><td>47151-1042</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1052</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1062</td><td></td><td>SEE NOTE 2 (4)</td></tr><tr><td>47151-2062</td><td>WITH</td><td>BLACK</td><td>SEE NOTE 2 (4)</td></tr><tr><td>47151-1012</td><td>W/O</td><td>NATURE</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1072</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1082</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1022</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-1032</td><td>NATURE</td><td>SEE NOTE 2 (1)</td><td></td></tr><tr><td>47151-1102</td><td rowspan="9">1.45</td><td rowspan="9">1.45</td><td rowspan="9">M3.0X0.5</td><td rowspan="9">16.08</td><td rowspan="9">13.38</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td>W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="9">SEE NOTE 2 (a)</td></tr><tr><td>47151-1142</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1152</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1112</td><td></td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1162</td><td>NATURE</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1172</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1122</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td>SEE NOTE 2 (b)</td></tr><tr><td>47151-1132</td><td>NATURE</td><td>SEE NOTE 2 (1)</td><td></td></tr><tr><td>47151-1005</td><td rowspan="9">1.80</td><td rowspan="9">2.20</td><td rowspan="9">4-40</td><td rowspan="9">16.08</td><td rowspan="9">13.38</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td>W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td><td rowspan="9">SEE NOTE 2 (a)</td></tr><tr><td>47151-1045</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1065</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1015</td><td></td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1035</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1055</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1025</td><td>WITH</td><td>BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-1075</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-1085</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-1026</td><td></td><td>SEE NOTE 2 (1)</td><td rowspan="9">SEE NOTE 2 (a)</td></tr><tr><td>47151-6012</td><td rowspan="9">1.80</td><td rowspan="9">2.20</td><td rowspan="9">M3.0X0.5</td><td rowspan="9">14.25</td><td rowspan="9">11.28</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td rowspan="9">WITH</td><td>W/O</td><td>BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6042</td><td></td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6052</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6022</td><td></td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6032</td><td></td><td>SEE NOTE 2 (3)</td></tr><tr><td>47151-6112</td><td rowspan="3">1.45</td><td rowspan="3">1.45</td><td rowspan="3"></td><td rowspan="3"></td><td rowspan="3"></td><td rowspan="3"></td><td rowspan="3"></td><td rowspan="3">W/O</td><td rowspan="3">BLACK</td><td>SEE NOTE 2 (1)</td></tr><tr><td>47151-6142</td><td>SEE NOTE 2 (2)</td></tr><tr><td>47151-6152</td><td>SEE NOTE 2 (3)</td></tr></table>											ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA	SHELL PLATING	REMARK	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR	47151-1002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 4	47151-1042		SEE NOTE 2 (2)	47151-1052		SEE NOTE 2 (3)	47151-1062		SEE NOTE 2 (4)	47151-2062	WITH	BLACK	SEE NOTE 2 (4)	47151-1012	W/O	NATURE	SEE NOTE 2 (1)	47151-1072		SEE NOTE 2 (2)	47151-1082		SEE NOTE 2 (3)	47151-1022	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-1032	NATURE	SEE NOTE 2 (1)		47151-1102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-1142		SEE NOTE 2 (2)	47151-1152		SEE NOTE 2 (3)	47151-1112		SEE NOTE 2 (1)	47151-1162	NATURE	SEE NOTE 2 (2)	47151-1172		SEE NOTE 2 (3)	47151-1122	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)	47151-1132	NATURE	SEE NOTE 2 (1)		47151-1005	1.80	2.20	4-40	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-1045		SEE NOTE 2 (2)	47151-1065		SEE NOTE 2 (3)	47151-1015		SEE NOTE 2 (1)	47151-1035		SEE NOTE 2 (2)	47151-1055		SEE NOTE 2 (3)	47151-1025	WITH	BLACK	SEE NOTE 2 (1)	47151-1075		SEE NOTE 2 (2)	47151-1085		SEE NOTE 2 (3)	47151-1026		SEE NOTE 2 (1)	SEE NOTE 2 (a)	47151-6012	1.80	2.20	M3.0X0.5	14.25	11.28	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	47151-6042		SEE NOTE 2 (2)	47151-6052		SEE NOTE 2 (3)	47151-6022		SEE NOTE 2 (1)	47151-6032		SEE NOTE 2 (3)	47151-6112	1.45	1.45						W/O	BLACK	SEE NOTE 2 (1)	47151-6142	SEE NOTE 2 (2)	47151-6152	SEE NOTE 2 (3)	F
ASSEMBLY P/N	DIMENSION					FEATURE				HOUSING COLOUR	GOLD PLATING IN CONACT AREA		SHELL PLATING	REMARK																																																																																																																																																																																							
	DIM A	DIM B	DIM C	DIM D	DIM E	FLANGE	BACK COVER	TOP HOLES	MYLAR																																																																																																																																																																																												
47151-1002	1.80	2.20	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)	FOR SHEET 4																																																																																																																																																																																								
47151-1042										SEE NOTE 2 (2)																																																																																																																																																																																											
47151-1052										SEE NOTE 2 (3)																																																																																																																																																																																											
47151-1062										SEE NOTE 2 (4)																																																																																																																																																																																											
47151-2062									WITH	BLACK	SEE NOTE 2 (4)																																																																																																																																																																																										
47151-1012									W/O	NATURE	SEE NOTE 2 (1)																																																																																																																																																																																										
47151-1072										SEE NOTE 2 (2)																																																																																																																																																																																											
47151-1082										SEE NOTE 2 (3)																																																																																																																																																																																											
47151-1022									BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																										
47151-1032	NATURE	SEE NOTE 2 (1)																																																																																																																																																																																																			
47151-1102	1.45	1.45	M3.0X0.5	16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																																									
47151-1142										SEE NOTE 2 (2)																																																																																																																																																																																											
47151-1152										SEE NOTE 2 (3)																																																																																																																																																																																											
47151-1112										SEE NOTE 2 (1)																																																																																																																																																																																											
47151-1162									NATURE	SEE NOTE 2 (2)																																																																																																																																																																																											
47151-1172										SEE NOTE 2 (3)																																																																																																																																																																																											
47151-1122									BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (b)																																																																																																																																																																																										
47151-1132									NATURE	SEE NOTE 2 (1)																																																																																																																																																																																											
47151-1005									1.80	2.20	4-40			16.08	13.38	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																															
47151-1045		SEE NOTE 2 (2)																																																																																																																																																																																																			
47151-1065		SEE NOTE 2 (3)																																																																																																																																																																																																			
47151-1015		SEE NOTE 2 (1)																																																																																																																																																																																																			
47151-1035		SEE NOTE 2 (2)																																																																																																																																																																																																			
47151-1055		SEE NOTE 2 (3)																																																																																																																																																																																																			
47151-1025	WITH	BLACK	SEE NOTE 2 (1)																																																																																																																																																																																																		
47151-1075		SEE NOTE 2 (2)																																																																																																																																																																																																			
47151-1085		SEE NOTE 2 (3)																																																																																																																																																																																																			
47151-1026		SEE NOTE 2 (1)	SEE NOTE 2 (a)																																																																																																																																																																																																		
47151-6012	1.80	2.20		M3.0X0.5	14.25	11.28	WITH	WITH	WITH	W/O	BLACK	SEE NOTE 2 (1)																																																																																																																																																																																									
47151-6042											SEE NOTE 2 (2)																																																																																																																																																																																										
47151-6052											SEE NOTE 2 (3)																																																																																																																																																																																										
47151-6022											SEE NOTE 2 (1)																																																																																																																																																																																										
47151-6032											SEE NOTE 2 (3)																																																																																																																																																																																										
47151-6112										1.45	1.45							W/O	BLACK	SEE NOTE 2 (1)																																																																																																																																																																																	
47151-6142																				SEE NOTE 2 (2)																																																																																																																																																																																	
47151-6152																				SEE NOTE 2 (3)																																																																																																																																																																																	
E														E																																																																																																																																																																																							
D												D																																																																																																																																																																																									
C												C																																																																																																																																																																																									
B												B																																																																																																																																																																																									
A	<table><tr><td rowspan="10">REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC500 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20</td><td rowspan="10">L1</td><td rowspan="10">REV</td><td rowspan="10">DESCRIPTION</td><td rowspan="10">QUALITY SYMBOLS</td><td rowspan="10">F_A=0 F_G=0 F_P=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="10"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="2">mm</td><td rowspan="2">INCH</td><td>DRAWN BY</td><td>DATE</td><td rowspan="5">TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>RZHANG</td><td>2004/07/20</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>2 PLACES</td><td>± 0.25</td><td>± ---</td><td>GRMA</td><td>2004/07/20</td></tr><tr><td>1 PLACE</td><td>± 0.25</td><td>± ---</td><td>APPROVED BY</td><td>DATE</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td>YTYAP</td><td>2004/07/20</td><td></td></tr><tr><td colspan="6">ANGULAR ± 3 °</td><td colspan="2">MATERIAL NO.</td><td colspan="2">SEE SHEET 6</td><td colspan="2">DOCUMENT NO. SD-47151-001</td><td>SHEET NO. 8 OF 8</td></tr><tr><td colspan="6">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="6">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>											REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC500 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20	L1	REV	DESCRIPTION	QUALITY SYMBOLS	F _A =0 F _G =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	mm	INCH	DRAWN BY	DATE	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE	4 PLACES	± ---	± ---	RZHANG	2004/07/20	3 PLACES	± ---	± ---	CHECKED BY	DATE	2 PLACES	± 0.25	± ---	GRMA	2004/07/20	1 PLACE	± 0.25	± ---	APPROVED BY	DATE	0 PLACE	±	±	YTYAP	2004/07/20		ANGULAR ± 3 °						MATERIAL NO.		SEE SHEET 6		DOCUMENT NO. SD-47151-001		SHEET NO. 8 OF 8	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						A																																																																																																																			
REVISE NOTE EC NO: S2014-0536 2013/12/05 DRWN:FC500 CHKD:JTAN02 2013/12/17 APPR:KHLIM 2013/12/20	L1	REV	DESCRIPTION	QUALITY SYMBOLS	F _A =0 F _G =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC							THIRD ANGLE PROJECTION																																																																																																																																																																																			
						mm	INCH	DRAWN BY	DATE	TITLE 1.0 HDMI RIGHT ANGLE HEADER ASSEMBLY(19 PIN) LEAD FREE																																																																																																																																																																																											
								4 PLACES	± ---		± ---								RZHANG	2004/07/20																																																																																																																																																																																	
						3 PLACES	± ---	± ---	CHECKED BY		DATE																																																																																																																																																																																										
						2 PLACES	± 0.25	± ---	GRMA		2004/07/20																																																																																																																																																																																										
						1 PLACE	± 0.25	± ---	APPROVED BY		DATE																																																																																																																																																																																										
						0 PLACE	±	±	YTYAP	2004/07/20																																																																																																																																																																																											
						ANGULAR ± 3 °													MATERIAL NO.		SEE SHEET 6		DOCUMENT NO. SD-47151-001		SHEET NO. 8 OF 8																																																																																																																																																																												
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																	
							fb_frame_A3_P_AM.T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																																																																																																																																																																					