


Miniature Paddle Switches



Contact Rating: 6 A @ 125 VAC, 3 A @ 250 VAC. UL Recognized, CSA Certified. Coin silver contacts, solder lug terminals, includes mounting hardware.

Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-99	100-249
747-6018	B121J2Z02	SPDT	On-Off-On	5.96	5.38	5.08
747-6019	B123J2Z02	SPDT	On-None-On	5.62	5.00	4.76
747-6020	B127J2Z02	SPDT	(On)-Off-(On)	5.96	5.38	5.08
747-6021	B221J2Z02	DPDT	On-Off-On	8.33	7.55	7.03
747-6022	B223J2Z02	DPDT	On-None-On	7.48	6.82	6.48
747-6023	B227J2Z02	DPDT	(On)-Off-(On)	8.33	7.55	7.03
747-6024	B321J2Z02	3PDT	On-Off-On	12.93	11.41	10.74
747-6025	B323J2Z02	3PDT	On-None-On	11.91	10.49	9.81
747-6026	B423J2Z02	4PDT	On-None-On	16.17	14.78	13.96



PB Series Pushbutton Switches


Maintained and Momentary
Panel mount. PB series with 3 cap sizes and colors, sold separately. See table below.
Specifications. Contact Rating: 6 A @ 125 VAC; 3 A @ 250 VAC; 6 A @ 28 VDC, resistive (UL listed). 100,000 make-and-break cycles for maintained models; 60,000 for momentary, resistive load only. Coin silver contacts. Solder lugs. Other terminals styles available upon request.

Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-99	100-249
747-0780	PB-12300ZQ	SPDT	On-On	4.98	3.96	3.45
747-0781	PB-12600ZQ	SPDT	On-(On)	5.18	4.12	3.57

Caps for Above

747-0784. W-KN-14. Black. .375 Dia.EACH	.23	747-0900. W-KN-31. Black. .310 Dia.EACH	.19
747-0785. W-KN-14A. White. .375 Dia.EACH	.24	747-0901. W-KN-31A. White. .310 Dia.EACH	.27
747-0786. W-KN-14B. Red. .375 Dia.EACH	.21	747-0902. W-KN-31B. Red. .310 Dia.EACH	.19
747-0789. W-KN-12B. Red. .200 Dia.EACH	.17		

Momentary Snap Action



Specifications. Contact Rating: 5 A resistive (1 pole), 1 A resistive (2 pole) @ 125 VAC or 28 VDC (UL listed) or 0.4 Volt-amp (VA) maximum @ 28 V max. (AC or DC), 60,000 cycles minimum at full load resistive. Center and End Contact: 1 and 5 A, brass, silver inlay and gold flash for solderability. .4 VA — brass, 50 millionth gold plated over nickel. Epoxy seal is standard. Caps sold separately.


Stock No.	Mfr.'s Type	Circuit	Terminal/ Rating	EACH		
				1-24	25-99	100-249
747-0790	PS1-100Q	SPDT	S.L. 5 A	6.07	5.66	4.72
747-0793	PS2-100B	SPDT	PC. 4 VA	7.03	5.46	4.77
747-0794	PS1-200Q	DPDT	S.L. 1 A	10.05	7.98	6.71
747-0795	PS2-200Q	DPDT	PC 1A	11.16	8.93	7.60
747-0796	PS1-200B	DPDT	S.L. .4 VA	9.43	7.29	6.40

Caps for Above

747-8800. W-KN-16B. Red. .200 Dia.EACH	.21	747-8805. W-KN-18A. White. .450 Sq. Dia.EACH	.24
747-0804. W-KN-18. Black. .450 Sq. Dia.EACH	.24	747-8806. W-KN-18B. Red. .450 Sq. Dia.EACH	.24


PCB Subminiature Pushbutton Switch

"Crossed Wire" contact system eliminates bounce. High contact pressure gives low contact resistance. Drain holes permit complete flux washdown. Solid silver contacts with gold over nickel plate. Momentary or latch-down (depress plunger and rotate 30° clockwise) operation. Current Ratings: 1 A @ 6 VDC and 12 VDC; 0.5 A @ 28 VAC and 125 VAC. 2 circuit poles and throw. Right angle PC mounting. Note: Optional snap-on buttons should be ordered separately.



747-0100. B8500. 0.160" (4.1 mm) Terminal Length. 1-24						
25-49	EACH	3.13	50-99			EACH 3.59
747-0281. P281R. Red Snap-On Button. 1-24						EACH .33
25-49	EACH	.24	50-99			EACH .21
747-0282. P281B. Black Snap-On Button. 1-24						EACH .33
25-49	EACH	.24	50-99			EACH .21


Miniature Rocker Switches



Contact Rating: 6 A @ 125 VAC, 3 A @ 250 VAC. UL Recognized, CSA Certified. Coin silver contacts, solder lug terminals, includes mounting hardware.

Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-99	100-249
747-6000	B121J1Z02	SPDT	On-Off-On	5.96	5.38	5.08
747-6001	B123J1Z02	SPDT	On-None-On	5.62	5.00	4.76
747-6002	B127J1Z02	SPDT	(On)-Off-(On)	5.96	5.38	5.08
747-6003	B221J1Z02	DPDT	On-Off-On	8.33	7.55	7.03
747-6004	B223J1Z02	DPDT	On-None-On	7.48	6.82	6.48
747-6005	B227J1Z02	DPDT	(On)-Off-(On)	8.33	7.55	7.03
747-6006	B321J1Z02	3PDT	On-Off-On	12.93	11.41	10.74
747-6007	B323J1Z02	3PDT	On-None-On	11.91	10.49	9.81
747-6008	B423J1Z02	4PDT	On-None-On	16.16	14.78	13.96
747-6009	B121J3Z02	SPDT	On-Off-On	5.96	5.38	5.08
747-6010	B123J3Z02	SPDT	On-None-On	5.62	5.00	4.76
747-6011	B127J3Z02	SPDT	(On)-Off-(On)	5.96	5.38	5.08
747-6012	B221J3Z02	DPDT	On-Off-On	8.33	7.55	7.03
747-6013	B223J3Z02	DPDT	On-None-On	7.48	6.82	6.48
747-6014	B227J3Z02	DPDT	(On)-Off-(On)	8.33	7.55	7.03
747-6015	B321J3Z02	3PDT	On-Off-On	12.93	11.41	10.74
747-6016	B323J3Z02	3PDT	On-None-On	11.91	10.49	9.81
747-6017	B423J3Z02	4PDT	On-None-On	16.16	14.78	13.96

Miniature Toggle Switches



Panel Mount

One hole mounting. 1/4" threaded bushing, bat lever. Contact Rating: 6 A @ 225 VAC/28 VDC; 3 A @ 250 VAC. UL Listed. Coin silver contacts, solder lug terminals. Includes mounting hardware.


Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-99	100-Up
747-3351	A121S1YZQ	SPDT	On-Off-On	4.16	3.39	2.92
747-3353	A123S1YZQ	SPDT	On-None-On	3.73	3.03	2.61
747-3356	A126S1YZQ	SPDT	On-None-(On)	4.99	4.06	3.50
747-3357	A127S1YZQ	SPDT	(On)-Off-(On)	4.16	3.39	2.92
747-3361	A131S1YZQ	SPDT	On-Off-(On)	6.24	5.08	4.37
747-3381	A221S1YZQ	DPDT	On-Off-On	5.78	4.78	4.17
747-3383	A223S1YZQ	DPDT	On-None-On	5.84	4.84	4.22
747-3386	A226S1YZQ	DPDT	On-None-(On)	7.19	5.93	5.17
747-3387	A227S1YZQ	DPDT	(On)-Off-(On)	6.85	5.76	5.03
747-3392	A232S1YZQ	DPDT	On-On-On	9.67	7.91	6.87
747-3422	A321S1YZQ	3PDT	On-Off-On	14.70	11.39	9.89
747-3423	A323S1YZQ	3PDT	On-None-On	11.09	8.58	7.42
747-3451	A421S1YZQ	4PDT	On-Off-On	19.17	16.12	14.11
747-3453	A423S1YZQ	4PDT	On-None-On	14.70	12.44	10.90

PC Mount

Same as panel mount except they are furnished with straight terminals. Terminals are gold flash over silver. Epoxy seal standard. Rating: 5 A @ 28 V AC/DC. Includes mounting hardware.

747-9501	A121S1YQC	SPDT	On-Off-On	5.55	4.52	3.91
747-9503	A123S1YQC	SPDT	On-None-On	3.82	3.11	2.69
747-9505	A221S1YQC	DPDT	On-Off-On	7.35	6.10	5.34
747-9507	A223S1YQC	DPDT	On-None-On	6.53	5.44	4.76

Miniature Flat Handle and Lever-Lock Switches



Flat Handle: Flat lever — brass, satin chrome finish. Rated: 6 A @ 125 VAC, 28 VDC; 3 A @ 250 VAC. UL listed. Solder lug terminals. Lever Lock: Prevents accidental actuation — lever must be lifted and moved to other position. All switches include mounting hardware.

Stock No.	Mfr.'s Type	Circuit	Action	EACH		
				1-24	25-99	100-Up
747-3321	A121P32Y5ZQ	SPDT	On-Off-On	7.54	6.36	5.64
747-3323	A123P32Y5ZQ	SPDT	On-None-On	8.38	7.06	6.27
747-3203	A123K12KZQ*	SPDT	On-None-On	7.60	6.25	5.69
747-3414	A221P32Y5ZQ	DPDT	On-Off-On	10.27	8.85	7.89
747-3416	A223P32Y5ZQ	DPDT	On-None-On	6.70	5.71	5.10
747-3213	A223K12KZQ*	DPDT	On-None-On	9.03	7.98	7.24

*Lever lock.