


Patch Cords

Stacking Banana Plug




Brass body, beryllium copper spring. Insulation: Polypropylene. Wire: 18 AWG, 65 × 36 t.c., PVC insulated, 3.66 mm (.144) O.D. Rating: 5000 VDC; 15 amps, +55°C (+131°F) max.		
885-0025, B-4-0, Black, 4"	EACH	3.70
885-0026, B-4-2, Red, 4"	EACH	3.70
885-0027, B-8-0, Black, 8"	EACH	3.70
885-0028, B-8-2, Red, 8"	EACH	3.70
885-0014, B-12-0, Black, 12"	EACH	3.70
885-0019, B-12-2, Red, 12"	EACH	3.70
885-0015, B-18-0, Black, 18"	EACH	3.70
885-0020, B-18-2, Red, 18"	EACH	3.70
885-0016, B-24-0, Black, 24"	EACH	3.70
885-0022, B-24-2, Red, 24"	EACH	3.70
885-0017, B-36-0, Black, 36"	EACH	3.70
885-0029, B-36-2, Red, 36"	EACH	3.70
885-0018, B-48-0, Black, 48"	EACH	4.10
885-0030, B-48-2, Red, 48"	EACH	4.10
885-4004, B-60-0, Black, 60"	EACH	4.10
885-4005, B-60-2, Red, 60"	EACH	4.10
885-4006, B-72-0, Black, 72"	EACH	4.10
885-4007, B-72-2, Red, 72"	EACH	4.10

Miniature Stacking Banana Plug Each End



1st End: Stacking miniature banana plug. Brass body, beryllium copper spring, gold plated. Insulation: Polypropylene. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.2 (.087) O.D. 2nd End: Stacking miniature banana plug. Brass body, beryllium copper spring, gold plated. Insulation: Polypropylene. Rating: 3000 VDC, 5 amps, +55°C (+131°F) max.		
885-1084, 1081-12-0, Black, 12"	EACH	5.05
885-1085, 1081-12-2, Red, 12"	EACH	5.05
885-1086, 1081-18-0, Black, 18"	EACH	5.05
885-1087, 1081-18-2, Red, 18"	EACH	5.05
885-1088, 1081-24-0, Black, 24"	EACH	5.05
885-1089, 1081-24-2, Red, 24"	EACH	5.05
885-1090, 1081-36-0, Black, 36"	EACH	5.05
885-1091, 1081-36-2, Red, 36"	EACH	5.05
885-1092, 1081-48-0, Black, 48"	EACH	5.40
885-1093, 1081-48-2, Red, 48"	EACH	5.40
885-1094, 1081-60-0, Black, 60"	EACH	5.40
885-1095, 1081-60-2, Red, 60"	EACH	5.40

Minigrabber® Test Clip to Stacking Banana Plug



1st End: Minigrabber®. Contact: Beryllium copper, gold plated. Insulation: Glass filled nylon. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.21 mm (.087) O.D. 2nd End: Stacking banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polypropylene. Rating: 300 VAC, 5 amps, +55°C (+131°F) max.		
885-0920, 3782-12-0, Black, 12"	EACH	3.40
885-0921, 3782-12-2, Red, 12"	EACH	3.40
885-0922, 3782-24-0, Black, 24"	EACH	3.40
885-0923, 3782-24-2, Red, 24"	EACH	3.40
885-5446, 3782-36-0, Black, 36"	EACH	3.40
885-5447, 3782-36-2, Red, 36"	EACH	3.40
885-0924, 3782-48-0, Black, 48"	EACH	3.70
885-0925, 3782-48-2, Red, 48"	EACH	3.70
885-0926, 3782-60-0, Black, 60"	EACH	3.70
885-0927, 3782-60-2, Red, 60"	EACH	3.70

Minigrabber® Test Clips to Stacking Banana Plug on Coiled Cord

20 AWG wire. PVC insulated, 48" ±1" extended length. Rating: 300 VAC continuous duty, 5 amps, +55°C.		
885-4536, 4538-0, Black	EACH	9.90
885-4539, 4538-2, Red	EACH	9.90

Minigrabber® Test Clip to Minigator



1st End: Minigrabber®. Contact: Beryllium copper, gold plated. Insulation: Glass filled nylon. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.21 mm (.087) O.D. 2nd End: Minigator. Steel, nickel plated. Insulation: Vinyl. Rating: 45 VAC; 5 amps, +50°C (+122°F) max.		
885-0953, 4652-12-0, Black, 12"	EACH	5.40
885-0954, 4652-12-2, Red, 12"	EACH	5.40
885-0955, 4652-24-0, Black, 24"	EACH	5.40
885-0956, 4652-24-2, Red, 24"	EACH	5.40

Minigrabber® Test Clip One End Only



Wire: 20 AWG, 41 × 36 t.c. PVC insulated, 2.21 mm (.087) O.D. Rating: 300 VAC, 12 amps.		
885-0906, 3780-60-0, Black, 60"	EACH	2.65
885-0907, 3780-60-2, Red, 60"	EACH	2.65

Minigrabber® Test Clip Each End



Wire: 20 AWG, 41 × t.c. PVC insulated, 2.21 mm (.087) O.D. Rating: 300 VAC, 12 amps.		
885-5432, 3781-8-0, Black, 8"	EACH	3.40
885-5433, 3781-8-2, Red, 8"	EACH	3.40
885-0910, 3781-12-0, Black, 12"	EACH	3.40
885-0911, 3781-12-2, Red, 12"	EACH	3.40
885-0916, 3781-18-0, Black, 18"	EACH	3.40
885-0917, 3781-18-2, Red, 18"	EACH	3.40
885-0912, 3781-24-0, Black, 24"	EACH	3.40
885-0913, 3781-24-2, Red, 24"	EACH	3.40
885-5438, 3781-36-0, Black, 36"	EACH	3.40
885-5439, 3781-36-2, Red, 36"	EACH	3.40
885-0914, 3781-48-0, Black, 48"	EACH	3.70
885-0915, 3781-48-2, Red, 48"	EACH	3.70
885-0918, 3781-60-0, Black, 60"	EACH	3.70
885-0919, 3781-60-2, Red, 60"	EACH	3.70


Minigrabber® Test Clip Patch Cord Kit

Kit contains 10 pieces of model 3781-24. One of each color.		
885-6027, 5523	EACH	30.15

Micrograbber® Test Clip to Stacking Banana Plug

20 AWG PVC insulated wire. Rating: 150 VAC, 3 amps, +55°C.		
885-5053, 5053-12-0, Black, 12"	EACH	5.35
885-5054, 5053-12-2, Red, 12"	EACH	5.35
885-5055, 5053-24-0, Black, 24"	EACH	5.35
885-5057, 5053-24-2, Red, 24"	EACH	5.35
885-5058, 5053-36-0, Black, 36"	EACH	5.35
885-5059, 5053-36-2, Red, 36"	EACH	5.35
885-5060, 5053-48-0, Black, 48"	EACH	5.65
885-5061, 5053-48-2, Red, 48"	EACH	5.65

Micrograbber® Each End



1st End: Micrograbber®. Contact: Beryllium copper, gold plated. Insulation: Glass filled nylon. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.21 mm (.087) O.D. 2nd End: Same as first end. Rating: 150 VAC, 3 amps; +102°C (+216°F) max.		
885-4613, 4613-12-0, Black, 12"	EACH	5.45
885-4614, 4613-12-2, Red, 12"	EACH	5.45
885-4615, 4613-24-0, Black, 24"	EACH	5.45
885-4616, 4613-24-2, Red, 24"	EACH	5.45
885-4617, 4613-36-0, Black, 36"	EACH	5.45
885-4618, 4613-36-2, Red, 36"	EACH	5.45
885-4619, 4613-48-0, Black, 48"	EACH	5.45
885-4620, 4613-48-2, Red, 48"	EACH	5.45

Micrograbber® Test Clip Patch Cord Kit

Kit contains 10 pieces of model 4613-24. One each of ten colors.		
885-6026, 5525	EACH	49.00

Insulated Alligator Clip Each End



18 AWG. Rated: 150 VAC, 5 amps, +50°C.		
885-0060, AL-B-12-0, Black, 12"	EACH	4.10
885-0061, AL-B-12-2, Red, 12"	EACH	4.10
885-0062, AL-B-24-0, Black, 24"	EACH	4.10
885-0063, AL-B-24-2, Red, 24"	EACH	4.10
885-0064, AL-B-36-0, Black, 36"	EACH	4.10
885-0065, AL-B-36-2, Red, 36"	EACH	4.10

Insulated Alligator Clip Kit

885-3907, 6356-36, Kit of 10 different colors, 36"	EACH	39.00
--	------	-------

Stacking Pin Tip Plug




Brass body, beryllium copper spring, gold plated. Insulation: Polypropylene. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.21 mm (.087) O.D. Rating: 3000 WVDC; 5 amps; +55°C (+131°F) max.		
885-0050, P-4-0, Black, 4"	EACH	4.45
885-0051, P-4-2, Red, 4"	EACH	4.45
885-0052, P-8-0, Black, 8"	EACH	4.45
885-0053, P-8-2, Red, 8"	EACH	4.45
885-0011, P-12-0, Black, 12"	EACH	4.45
885-0012, P-12-2, Red, 12"	EACH	4.45
885-0013, P-18-0, Black, 18"	EACH	4.45
885-0054, P-18-2, Red, 18"	EACH	4.45
885-0055, P-24-0, Black, 24"	EACH	4.45
885-0056, P-24-2, Red, 24"	EACH	4.45
885-0057, P-36-0, Black, 36"	EACH	4.45
885-0058, P-36-2, Red, 36"	EACH	4.45

Test Lead Holder



Stock No.	Mfr.'s Type	Color	Dia.	Slots	EACH
885-0382	1508	Orange	0.210"	14	5.85
885-4408	4408	Black	0.320"	10	5.85
885-0631	2708	Blue	0.450"	9	5.85

Stacking Banana Plug to Stacking Pin Tip Plug



Adapts to equipment using banana jacks and pin jacks. Banana plug and pin tip allow vertical stackup. 1st End: Stacking banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polypropylene. Wire: 20 AWG, 41 × 36 t.c., PVC insulated, 2.2 (.087) O.D. 2nd End: Stacking pin tip plug. Brass body, beryllium copper spring, gold plated. Insulation: Polypropylene. Rating: 3000 VDC, 5 amps, +55°C (+131°F) max.		
885-1129, 1126-12-0, Black, 12"	EACH	4.35
885-1130, 1126-12-2, Red, 12"	EACH	4.35
885-1131, 1126-18-0, Black, 18"	EACH	4.35
885-1132, 1126-18-2, Red, 18"	EACH	4.35
885-1133, 1126-24-0, Black, 24"	EACH	4.35
885-1134, 1126-24-2, Red, 24"	EACH	4.35
885-1135, 1126-36-0, Black, 36"	EACH	4.35
885-1136, 1126-36-2, Red, 36"	EACH	4.35
885-1137, 1126-48-0, Black, 48"	EACH	4.55
885-1138, 1126-48-2, Red, 48"	EACH	4.55
885-1139, 1126-60-0, Black, 60"	EACH	4.55
885-1140, 1126-60-2, Red, 60"	EACH	4.55

Banana Plug to In-Line Banana Jack



Dual purpose. Insulates all hot leads when used as an extension cord. Endless extension couplings possible with any banana plug patch cord. 1st End: Banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polypropylene. Wire: 18 AWG, 65 × 36 t.c., PVC insulated, 3.7 (.144) O.D. 2nd End: In-line banana jack. Brass, nickel plated. Insulation: Polypropylene. Rating: 5000 VDC, 15 amps, +55°C (+131°F) max.		
885-4700, 4702-12-0, Black, 12"	EACH	4.95
885-4701, 4702-12-2, Red, 12"	EACH	4.95
885-4702, 4702-18-0, Black, 18"	EACH	4.95
885-4703, 4702-18-2, Red, 18"	EACH	4.95
885-4704, 4702-24-0, Black, 24"	EACH	4.95
885-4705, 4702-24-2, Red, 24"	EACH	4.95
885-4706, 4702-36-0, Black, 36"	EACH	4.95
885-4707, 4702-36-2, Red, 36"	EACH	4.95
885-4708, 4702-48-0, Black, 48"	EACH	5.15
885-4709, 4702-48-2, Red, 48"	EACH	5.15
885-4710, 4702-60-0, Black, 60"	EACH	5.15
885-4711, 4702-60-2, Red, 60"	EACH	5.15

Extension Stacking Banana Plug Each End



Dual purpose. Insulates all hot leads when used as an extension cord. Endless extension couplings possible with any banana plug patch cord. 1st End: Extension stacking banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polypropylene. Wire: 18 AWG, 65 × 36 t.c., PVC insulated, 3.7 (.144) O.D. 2nd End: Extension stacking banana plug. Brass body, beryllium copper spring, nickel plated. Insulation: Polypropylene. Rating: 5000 VDC, 15 amps, +55°C (+131°F) max.		
885-4008, HB-12-0, Black, 12"	EACH	5.85
885-4009, HB-12-2, Red, 12"	EACH	5.85
885-4010, HB-24-0, Black, 24"	EACH	5.85
885-4011, HB-24-2, Red, 24"	EACH	5.85
885-4012, HB-36-0, Black, 36"	EACH	5.85
885-4013, HB-36-2, Red, 36"	EACH	5.85
885-9984, HB-48-0, Black, 48"	EACH	6.25
885-9983, HB-48-2, Red, 48"	EACH	6.25

Alligator Clip to Stacking Banana



1st End: Alligator clip. Steel, nickel plated. Vinyl boot. Wire: 18 AWG, 65 × 36 t.c., PVC insulated, 3.7 (.144) O.D. 2nd End: Stacking banana plug. Brass body, beryllium copper, gold plated. Insulation: Polypropylene. Rating: 150 VAC, 5 amps, +50°C (+122°F) max.		
885-1166, 1166-4-0, Black, 4"	EACH	4.10
885-1167, 1166-4-2, Red, 4"	EACH	4.10
885-1168, 1166-8-0, Black, 8"	EACH	4.10
885-1169, 1166-8-2, Red, 8"	EACH	4.10
885-4040, 1166-12-0, Black, 12"	EACH	4.10
885-4041, 1166-12-2, Red, 12"	EACH	4.10
885-4042, 1166-24-0, Black, 24"	EACH	4.10
885-4043, 1166-24-2, Red, 24"	EACH	4.10
885-4045, 1166-36-0, Black, 36"	EACH	4.10
885-4046, 1166-36-2, Red, 36"	EACH	4.10
885-4047, 1166-48-0, Black, 48"	EACH	4.45
885-4048, 1166-48-2, Red, 48"	EACH	4.45
885-1170, 1166-60-0, Black, 60"	EACH	4.63
885-1171, 1166-60-2, Red, 60"	EACH	4.63

Alligator Clip to Stacking Banana Kit

885-9909, 6357-36, Kit of 10 colors, 36"	EACH	39.00
--	------	-------