

Angle Head Drills - Cordless

DW965K



12V heavy duty 10mm cordless right angle drill. Dual speed gearbox with reverse action. Multiple grip soft touch switch. Keyless chuck with electronic brake. Supplied with charger, 1 x 2.0Ah Ni Cd battery pack and carrying case.

Model Number	DW965K
Voltage	12.0 V
No Load Speed	0-400/0-1200 rpm
Drilling Capacity Steel	10 mm
Drilling Capacity Wood	25 mm
Battery	1 × 2.0Ah Ni Cd
Chuck Capacity	10mm
Weight	2.0 kg

		Price Each
Description	Order Code	
DW965K drill	135-3031	
Replacement battery DE9071	135-2976	

DW966K



14.4V, heavy duty 10mm cordless right angle drill. Dual speed gearbox with reverse action. Multiple grip soft touch switch. Keyless chuck with electronic brake. Supplied with charger, 1 x 2.0Ah Ni Cd battery pack and carrying case.

Model Number	DW966K
Voltage	14.4 V
No Load Speed	0-400/0-1250 rpm
Drilling Capacity Steel	10 mm
Drilling Capacity Wood	28 mm
Battery	1 × 2.0Ah Ni Cd
Chuck Capacity	10mm
Weight	2.1 kg

		Price Each
Description	Order Code	
DW966K drill	135-3033	
Replacement battery DE9091	135-2979	