


MALLORY**Mallory Sonalert Products Inc.****Part # PF-21A29PQ****Sales Outline Drawing**Revision **A****Specifications:**

Oscillation Frequency (Hz)	3000 \pm 500
Operating Voltage (VDC)	3 ~ 24
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	18 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 30cm at Rated Voltage
Tone / Pulse Rate	Fast Pulse 3.0 \pm 20%
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 777 UL94 HB plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	3.2
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PF-21A29PQ](#)