


LED Lamps



T3 mm, Size LED Lamps

Stock No.	Mfr.'s Type	Emitted Color	Wavelength Peak (nm)	Lens Color	IV mCD @ /mA	Viewing Angle	EACH
					1-99	100-999	1000-Up
670-1057	SSL-LX3044GD	Green	565	Green*	40/20	60	.10 .08 .07
670-1058	SSL-LX3044ID	Red	635	Red*	50/20	60	.10 .09 .07
670-1059	SSL-LX3044YD	Yellow	585	Yellow*	40/20	60	.10 .09 .07

Bi-Color Option

670-1060	SSL-LX3059IGW	Red/Green	635/565	White*	30/18/20	60	.35 .33 .30
----------	---------------	-----------	---------	--------	----------	----	-------------

T3 mm, Super Brite LEDs, Dome Lens

670-1061	SSL-LX3044GC	Green	565	Clear	100/20	50	.11 .09 .08
670-1062	SSL-LX3044YC	Yellow	585	Clear	90/20	50	.11 .09 .08
670-1063	SSL-LX3044SRC/B	Super Red	660	Clear	300/20	50	.25 .21 .17

T5 mm, Size LEDs (T-1 1/4)

670-1064	SSL-LX5093GD	Green	565	Green*	20/20	80	.10 .08 .07
670-1065	SSL-LX5093ID	Red	635	Red*	20/20	80	.10 .08 .07
670-1066	SSL-LX5093YD	Yellow	585	Yellow*	20/20	80	.10 .08 .07

Bi-Color Option

670-1067	SSL-LX5099IGW	Red/Green	635/565	White*	55/45/20	60	.23 .20 .17
670-1068	SSL-LX5099YGW	Yellow/Green	585/565	White*	40/45/20	60	.23 .20 .17

*Diffused. †Transparent.

Opto-Electronic Components

IR Emitting Diodes, T5

Stock No.	Mfr.'s Type	Lens Finish	Po (mW/sr) Type/(mA)	Vf (Vmax) If(mA)	λ Pk. (nm)	$\Delta\phi$ Typ.	EACH
					1-99	100-999	1000-Up
670-0136	OED-EL-1L1	Clear Epoxy	35.0/50	1.7/100	940	$\pm 10^\circ$.33 .30 .27
670-0137	OED-EL-1L2	Clear Epoxy	25.0/50	1.7/100	940	$\pm 30^\circ$.37 .30 .28


High Performance Diodes, Right Angle

670-0138	OED-CL-1556SN	Yellow Transp.	6.5/50	1.5/20	880	$\pm 10^\circ$.37 .32 .26
----------	---------------	----------------	--------	--------	-----	----------------	-------------

Phototransistors, Right Angle

Stock No.	Mfr.'s Type	Lens Finish	Ic(mA)@EV-1000 Lx Type/Vce(V)	λ Pk. (nm)	$\Delta\phi$ Typ.	EACH	
					1-99	100-999	1000-Up
670-0139	OED-ST-1556SN	Clear Epoxy	6.0/5.0	940	$\pm 11^\circ$.37 .32 .26	

LED Panel Holders



Stock No.	Mfr.'s Type	Construction	Application	Panel Hole Size	EACH
					1-99 100-999 1000-Up
670-1081	SSH-LX3050	Black Nylon, 1-Pc	3 mm LED Panel Holder	0.160"	.10 .08 .03

T5 mm, Super Brite LEDs, Dome Lens

Stock No.	Mfr.'s Type	Emitted Color	Wavelength Peak (nm)	Lens Color	IV mCD @ /mA	Viewing Angle	EACH
					1-99	100-999	1000-Up
670-1202	SSL-LX5093SRC/E	Super Red	660	Clear	3500/20	30	.52 .48 .34
670-1070	SSL-LX5093WC/B	Ultra White	550	Clear	1700/20	20	3.99 3.73 3.09
670-1071	SSL-LX5095UBC125	Ultra Blue	470	Clear	2000/20	15	6.26 5.42 4.42
670-1072	SSL-LX5095UPG6C125	Ultra Pure Green	525	Clear	5000/20	20	7.63 6.61 5.76

9


Rectangular LED Lamps

670-1200	SSL-LX2573GD	Green	565	Green*	10/20	80	.26 .14 .10
670-1075	SSL-LX2573ID	Red	635	Red*	10/20	80	.26 .14 .10
670-1073	SSL-LX2573YD	Yellow	585	Yellow*	10/20	80	.11 .10 .08
670-1074	SSL-LX2573SRD	Super Red	660	Red†	80/20	80	.17 .14 .12


9 mm, Side Firing Dual Chip LED Bars

670-1076	SSL-LX2579IGW	Red/Green	635/565	White*	14/8/20	80	.23 .20 .17
670-1077	SSL-LX2579YGW	Yellow/Green	585/565	White*	5/8/20	80	.23 .20 .17


OED-EL-1L2



OED-ST-1556SN



OED-CL-1556SN



Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com

ALLIED ► 557