

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0503293024

Status:

Obsolete

Description:

Spade Tongue Terminal for 14 and 16 AWG, Closed Insulated Vinyl Straight Barrel, Blue, Stud Size 6 (M3.5), Oxygen-Free Copper, Length 20.30mm (.799"), Clearance 7.10mm (.280")

Documents:

Drawing (PDF)

General

Product Family	Ring and Spade Terminals
Series	50329
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	VSY (Spade Vinyl Straight)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Color - Resin	Blue
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	6 (M3.5)
Wire Size AWG	14, 16
Wire Size mm²	1.04 - 2.63

Material Info

Reference - Drawing Numbers

Product Specification	PS-50328-002
Sales Drawing	SD-50329-001



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50329Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION