

Nut - A-INL-M40-P-GY - 1411210

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Nut, Cable gland material: Polyamide 6, PA 6 GF 30, For threads M40, Color: silver grey



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Custom tariff number	39269097
Country of origin	Turkey

Technical data

Dimensions

Length	7 mm
Connecting thread diameter	40 mm
Wrench size, counter nut	50 mm
Hexagon angular dimension GRP	55.3 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 100 °C
---------------------------------	-------------------

General

Material	PA 6 GF 30
Cable gland material	Polyamide 6
Flammability rating according to UL 94	V2
Color	silver-grey RAL 7001
	silver grey

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Nut - A-INL-M40-P-GY - 1411210

Classifications

eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 8.0	23110701

ETIM

ETIM 4.0	EC000032
ETIM 5.0	EC000129

Drawings

Dimensional drawing

